

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204914

Luminaire Tested: **LD6B40D010 EU6B30508040 6LBCSMB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204914
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B40D010 EU6B30508040 6LBCSMB1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH CAST MATTE BLACK TRIM
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57
W DL3-44.71 W DLE-39.33 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4016.0 lumens
Efficiency: N/A
Efficacy: 96.1 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204914

CATALOG NUMBER: LD6B40D010 EU6B30508040 6LBCSMB1

Luminous Intensity Polar Plot






TEST NUMBER: P204914

CATALOG NUMBER: LD6B40D010 EU6B30508040 6LBCSMB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	111	107	103	100	108	104	101	98		100	98	95		96	94	92		93	91	90
2	102	95	89	84	99	93	87	83		89	85	81		86	82	79		83	80	77
3	93	84	77	71	91	83	76	70		80	74	69		77	72	68		74	70	67
4	86	75	67	61	84	74	66	61		71	65	60		69	63	59		67	62	58
5	79	67	59	53	77	66	59	53		64	57	52		62	56	52		61	55	51
6	74	61	53	47	72	60	52	46		58	51	46		57	50	46		55	50	45
7	68	55	47	41	67	55	47	41		53	46	41		52	45	41		50	45	40
8	64	51	43	37	62	50	42	37		49	42	37		48	41	37		46	41	36
9	60	47	39	33	58	46	39	33		45	38	33		44	38	33		43	37	33
10	56	43	35	30	55	43	35	30		42	35	30		41	34	30		40	34	30

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204914

CATALOG NUMBER: LD6B40D010 EU6B30508040 6LBCSMB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	160.4	4.0
10°-20°	457.0	11.4
20°-30°	686.9	17.1
30°-40°	815.1	20.3
40°-50°	806.6	20.1
50°-60°	633.5	15.8
60°-70°	355.2	8.8
70°-80°	99.8	2.5
80°-90°	1.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1304.3	32.5
0°-40°	2119.3	52.8
0°-60°	3559.5	88.6
0°-90°	4016.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4016.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1696	
5°	1693	160
15°	1621	457
25°	1491	687
35°	1307	815
45°	1051	807
55°	714	634
65°	354	355
75°	86	100
85°	0	2
90°	0	



TEST NUMBER: P204914

CATALOG NUMBER: LD6B40D010 EU6B30508040 6LBCSMB1

CANDELA DISTRIBUTION (FULL):

0°	
0°	1695.8
2.5°	1690.0
5°	1692.9
7.5°	1678.5
10°	1661.2
12.5°	1641.1
15°	1620.9
17.5°	1595.0
20°	1560.5
22.5°	1525.9
25°	1491.4
27.5°	1453.9
30°	1405.0
32.5°	1356.1
35°	1307.1
37.5°	1249.5
40°	1183.3
42.5°	1120.0
45°	1050.9
47.5°	973.1
50°	892.5
52.5°	800.4
55°	714.0
57.5°	616.1
60°	524.0
62.5°	440.5
65°	354.1
67.5°	279.3
70°	207.3
72.5°	141.1
75°	86.4
77.5°	43.2
80°	11.5
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)