

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P202523

Luminaire Tested: **LD6B20D010 EU6B10209040 6LBSWMH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P202523
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B20D010 EU6B10209040 6LBSWMH1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH WARM HAZE TRIM
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W
DL3-21.8 6 W DLE-22.46 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1851.5 lumens
Efficiency: N/A
Efficacy: 89.0 lumens/watt
Spacing Criteria (0/90/45): 0.97 / 0.97 / 1.1
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P202523

CATALOG NUMBER: LD6B20D010 EU6B10209040 6LBSWMH1

Luminous Intensity Polar Plot






TEST NUMBER: P202523

CATALOG NUMBER: LD6B20D010 EU6B10209040 6LBSWMH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			0
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			100
1	111	107	104	101	108	105	102	99		101	98	96			97	95	93			88
2	103	96	90	85	100	94	89	84		91	86	82			87	84	81			77
3	95	86	79	73	92	84	78	73		81	76	71			79	74	70			67
4	88	77	70	64	86	76	69	63		74	67	62			71	66	62			59
5	81	70	62	56	79	69	61	56		67	60	55			65	59	55			52
6	76	64	56	50	74	63	55	50		61	54	49			59	53	49			47
7	70	58	50	45	69	57	50	45		56	49	44			55	48	44			42
8	66	54	46	40	64	53	45	40		52	45	40			50	44	40			38
9	62	49	42	37	61	49	42	37		48	41	37			47	41	36			35
10	58	46	39	34	57	45	38	34		45	38	34			44	38	33			32

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P202523

CATALOG NUMBER: LD6B20D010 EU6B10209040 6LBSWMH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	99.1	5.4
10°-20°	258.9	14.0
20°-30°	343.4	18.5
30°-40°	366.2	19.8
40°-50°	342.4	18.5
50°-60°	261.0	14.1
60°-70°	142.0	7.7
70°-80°	38.1	2.1
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	701.3	37.9
0°-40°	1067.6	57.7
0°-60°	1671.0	90.2
0°-90°	1851.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1851.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1071	
5°	1056	99
15°	923	259
25°	747	343
35°	585	366
45°	446	342
55°	294	261
65°	142	142
75°	33	38
85°	0	0
90°	0	



TEST NUMBER: P202523

CATALOG NUMBER: LD6B20D010 EU6B10209040 6LBSWMH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	1070.6
2.5°	1067.2
5°	1055.9
7.5°	1032.1
10°	1004.9
12.5°	966.3
15°	923.2
17.5°	880.1
20°	833.6
22.5°	789.4
25°	747.4
27.5°	703.2
30°	661.2
32.5°	620.4
35°	585.2
37.5°	550.1
40°	513.8
42.5°	480.9
45°	445.7
47.5°	407.2
50°	370.9
52.5°	332.3
55°	293.7
57.5°	251.8
60°	213.2
62.5°	176.9
65°	141.8
67.5°	110.0
70°	80.5
72.5°	55.6
75°	32.9
77.5°	14.7
80°	3.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)