

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203676

Luminaire Tested: **LD6B40D010 EU6B30508040 6LBNH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203676
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B40D010 EU6B30508040 6LBNH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57
W DL3-44.71 W DLE-39.33 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2721.9 lumens
Efficiency: N/A
Efficacy: 65.1 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.84
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203676

CATALOG NUMBER: LD6B40D010 EU6B30508040 6LBNH1

Luminous Intensity Polar Plot






TEST NUMBER: P203676

CATALOG NUMBER: LD6B40D010 EU6B30508040 6LBNH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	109	106	104	104	103	101		101	99	98		97
2	108	103	99	96	106	101	98	94	98	95	92		95	93	90		92
3	102	96	91	87	100	95	90	86	92	88	85		90	86	84		87
4	97	90	84	80	95	89	83	79	86	82	78		84	81	78		83
5	92	84	78	74	91	83	78	73	81	76	73		80	75	72		78
6	88	79	73	69	86	78	72	68	77	72	68		75	71	67		74
7	83	74	68	64	82	73	68	64	72	67	63		71	66	63		70
8	79	70	64	60	78	69	64	60	68	63	59		67	63	59		66
9	76	66	60	56	75	66	60	56	65	59	56		64	59	56		63
10	72	62	57	53	71	62	57	53	61	56	53		60	56	52		60

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203676

CATALOG NUMBER: LD6B40D010 EU6B30508040 6LBNH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	313.8	11.5
10°-20°	748.3	27.5
20°-30°	857.2	31.5
30°-40°	576.0	21.2
40°-50°	164.6	6.0
50°-60°	40.3	1.5
60°-70°	15.3	0.6
70°-80°	5.9	0.2
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1919.2	70.5
0°-40°	2495.2	91.7
0°-60°	2700.0	99.2
0°-90°	2721.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2721.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3489	
5°	3390	314
15°	2685	748
25°	1871	857
35°	918	576
45°	189	165
55°	45	40
65°	15	15
75°	5	6
85°	0	1
90°	0	



TEST NUMBER: P203676

CATALOG NUMBER: LD6B40D010 EU6B30508040 6LBNH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	3489.2
2.5°	3464.4
5°	3389.9
7.5°	3255.9
10°	3092.1
12.5°	2883.6
15°	2685.1
17.5°	2476.7
20°	2268.2
22.5°	2069.7
25°	1871.1
27.5°	1687.5
30°	1474.1
32.5°	1191.2
35°	918.2
37.5°	670.0
40°	461.6
42.5°	302.8
45°	188.6
47.5°	114.2
50°	69.5
52.5°	54.6
55°	44.7
57.5°	34.7
60°	24.8
62.5°	19.9
65°	14.9
67.5°	9.9
70°	9.9
72.5°	5.0
75°	5.0
77.5°	5.0
80°	5.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)