

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204077

Luminaire Tested: **LD6B30D010 EU6B30509024 6LBNMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204077
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B30D010 EU6B30509024 6LBNMW1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W
DL3-29.67 W DLE-29.73 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1541.2 lumens
Efficiency: N/A
Efficacy: 55.0 lumens/watt
Spacing Criteria (0/90/45): 0.99 / 0.99 / 0.97
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204077

CATALOG NUMBER: LD6B30D010 EU6B30509024 6LBNMW1

Luminous Intensity Polar Plot






TEST NUMBER: P204077

CATALOG NUMBER: LD6B30D010 EU6B30509024 6LBNMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	112	108	105	103		109	106	103	101		102	100	98		98	97	95		95	93	92
2	105	99	94	90		102	97	92	89		94	90	87		91	87	85		88	85	83
3	98	90	84	79		96	89	83	79		86	81	77		84	80	76		81	78	75
4	92	83	76	71		90	82	76	71		80	74	70		77	73	69		75	71	68
5	87	77	70	65		85	76	69	64		74	68	64		72	67	63		70	66	62
6	81	71	64	59		80	70	63	59		68	63	58		67	62	58		66	61	57
7	77	66	59	54		75	65	59	54		64	58	54		63	57	53		61	57	53
8	72	61	55	50		71	61	54	50		60	54	49		59	53	49		58	53	49
9	69	58	51	46		67	57	51	46		56	50	46		55	50	46		54	49	46
10	65	54	47	43		64	54	47	43		53	47	43		52	46	43		51	46	43

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204077

CATALOG NUMBER: LD6B30D010 EU6B30509024 6LBNMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	117.4	7.6
10°-20°	311.1	20.2
20°-30°	415.4	27.0
30°-40°	335.1	21.7
40°-50°	160.6	10.4
50°-60°	95.2	6.2
60°-70°	63.3	4.1
70°-80°	33.9	2.2
80°-90°	9.3	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	843.8	54.8
0°-40°	1178.9	76.5
0°-60°	1434.7	93.1
0°-90°	1541.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1541.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1264	
5°	1249	117
15°	1107	311
25°	909	415
35°	536	335
45°	198	161
55°	105	95
65°	64	63
75°	32	34
85°	7	9
90°	0	



TEST NUMBER: P204077

CATALOG NUMBER: LD6B30D010 EU6B30509024 6LBNMW1

CANDELA DISTRIBUTION (FULL):

0°	
0°	1264.0
2.5°	1264.0
5°	1249.3
7.5°	1224.8
10°	1190.5
12.5°	1153.8
15°	1107.2
17.5°	1063.1
20°	1014.1
22.5°	962.7
25°	908.8
27.5°	852.5
30°	771.6
32.5°	658.9
35°	536.5
37.5°	423.8
40°	328.2
42.5°	254.8
45°	198.4
47.5°	156.8
50°	132.3
52.5°	117.6
55°	105.3
57.5°	95.5
60°	83.3
62.5°	73.5
65°	63.7
67.5°	53.9
70°	46.5
72.5°	39.2
75°	31.8
77.5°	24.5
80°	19.6
82.5°	14.7
85°	7.3
87.5°	2.4
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)