

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205411

Luminaire Tested: **LD6B30D010 EU6B30509024 6LBSLI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205411
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B30D010 EU6B30509024 6LBSLI1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH SPECULAR CLEAR TRIM
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W
DL3-29.67 W DLE-29.73 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2302.1 lumens
Efficiency: N/A
Efficacy: 82.2 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1.04
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205411

CATALOG NUMBER: LD6B30D010 EU6B30509024 6LBSLI1

Luminous Intensity Polar Plot





TEST NUMBER: P205411

CATALOG NUMBER: LD6B30D010 EU6B30509024 6LBSLI1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			50
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			102
1	111	107	104	101	109	105	102	99		101	99	96			97	95	93			94
2	103	96	91	86	100	94	89	85		91	87	83			88	84	81			85
3	95	86	79	74	93	85	78	73		82	76	72			79	75	71			77
4	88	78	70	64	86	77	69	64		74	68	63			72	67	62			70
5	82	71	63	57	80	70	62	57		67	61	56			66	60	55			64
6	76	64	56	51	74	63	56	51		62	55	50			60	54	50			59
7	71	59	51	46	70	58	51	45		57	50	45			55	49	45			54
8	67	54	47	41	65	54	46	41		52	46	41			51	45	41			50
9	63	50	43	38	61	50	43	38		49	42	38			48	42	37			47
10	59	47	40	35	58	46	39	35		45	39	35			45	39	34			44

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205411

CATALOG NUMBER: LD6B30D010 EU6B30509024 6LBSLI1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	133.9	5.8
10°-20°	340.8	14.8
20°-30°	434.6	18.9
30°-40°	450.7	19.6
40°-50°	415.3	18.0
50°-60°	312.4	13.6
60°-70°	168.6	7.3
70°-80°	45.2	2.0
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	909.3	39.5
0°-40°	1359.9	59.1
0°-60°	2087.6	90.7
0°-90°	2302.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2302.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1453	
5°	1431	134
15°	1216	341
25°	944	435
35°	719	451
45°	540	415
55°	350	312
65°	169	169
75°	39	45
85°	0	1
90°	0	



TEST NUMBER: P205411

CATALOG NUMBER: LD6B30D010 EU6B30509024 6LBSLI1

CANDELA DISTRIBUTION (FULL):

0°	
0°	1452.7
2.5°	1447.9
5°	1430.7
7.5°	1398.9
10°	1342.7
12.5°	1286.4
15°	1215.5
17.5°	1149.5
20°	1081.0
22.5°	1010.1
25°	944.0
27.5°	880.5
30°	821.8
32.5°	767.9
35°	719.0
37.5°	672.6
40°	628.5
42.5°	582.1
45°	540.5
47.5°	494.0
50°	447.6
52.5°	398.6
55°	349.7
57.5°	300.8
60°	254.4
62.5°	210.3
65°	168.8
67.5°	129.6
70°	95.4
72.5°	66.0
75°	39.1
77.5°	17.1
80°	4.9
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)