

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P202749

Luminaire Tested: **LD6B40D010 EU6B30508040 6LBWH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P202749  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD6B40D010 EU6B30508040 6LBWH1  
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT  
WIDE DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM  
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57  
W DL3-44.71 W DLE-39.33 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3827.6 lumens  
Efficiency: N/A  
Efficacy: 91.6 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.16  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 41.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P202749

CATALOG NUMBER: LD6B40D010 EU6B30508040 6LBWH1

### Luminous Intensity Polar Plot





TEST NUMBER: P202749

CATALOG NUMBER: LD6B40D010 EU6B30508040 6LBWH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 112 | 109 | 106 | 103 | 110 | 107 | 104 | 101 | 103 | 100 | 98  |  | 99  | 97  | 95  |  | 95  |
| 2   | 105 | 99  | 94  | 90  | 103 | 97  | 93  | 89  | 94  | 90  | 87  |  | 91  | 88  | 85  |  | 88  |
| 3   | 98  | 90  | 84  | 79  | 96  | 89  | 83  | 78  | 86  | 81  | 77  |  | 83  | 79  | 76  |  | 81  |
| 4   | 92  | 82  | 75  | 70  | 90  | 81  | 75  | 70  | 79  | 73  | 69  |  | 77  | 72  | 68  |  | 75  |
| 5   | 86  | 75  | 68  | 63  | 84  | 74  | 68  | 63  | 72  | 66  | 62  |  | 71  | 65  | 61  |  | 69  |
| 6   | 80  | 69  | 62  | 57  | 78  | 68  | 61  | 56  | 67  | 61  | 56  |  | 65  | 60  | 56  |  | 64  |
| 7   | 75  | 64  | 56  | 51  | 73  | 63  | 56  | 51  | 62  | 55  | 51  |  | 60  | 55  | 51  |  | 59  |
| 8   | 70  | 59  | 52  | 47  | 69  | 58  | 51  | 47  | 57  | 51  | 46  |  | 56  | 50  | 46  |  | 55  |
| 9   | 66  | 55  | 48  | 43  | 65  | 54  | 47  | 43  | 53  | 47  | 43  |  | 52  | 47  | 42  |  | 51  |
| 10  | 62  | 51  | 44  | 40  | 61  | 50  | 44  | 39  | 50  | 43  | 39  |  | 49  | 43  | 39  |  | 48  |

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P202749

CATALOG NUMBER: LD6B40D010 EU6B30508040 6LBWH1

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 223.0  | 5.8       |
| 10°-20°   | 632.7  | 16.5      |
| 20°-30°   | 927.6  | 24.2      |
| 30°-40°   | 965.5  | 25.2      |
| 40°-50°   | 668.0  | 17.5      |
| 50°-60°   | 290.8  | 7.6       |
| 60°-70°   | 89.2   | 2.3       |
| 70°-80°   | 26.7   | 0.7       |
| 80°-90°   | 4.1    | 0.1       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 1783.3 | 46.6      |
| 0°-40°    | 2748.8 | 71.8      |
| 0°-60°    | 3707.6 | 96.9      |
| 0°-90°    | 3827.6 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 3827.6 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 2361 |      |
| 5°  | 2351 | 223  |
| 15° | 2247 | 633  |
| 25° | 2028 | 928  |
| 35° | 1562 | 965  |
| 45° | 863  | 668  |
| 55° | 312  | 291  |
| 65° | 84   | 89   |
| 75° | 25   | 27   |
| 85° | 5    | 4    |
| 90° | 0    |      |



TEST NUMBER: P202749

CATALOG NUMBER: LD6B40D010 EU6B30508040 6LBWH1

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     |
|-------|--------|
| 0°    | 2360.8 |
| 2.5°  | 2365.7 |
| 5°    | 2350.8 |
| 7.5°  | 2331.0 |
| 10°   | 2306.2 |
| 12.5° | 2281.4 |
| 15°   | 2246.7 |
| 17.5° | 2202.1 |
| 20°   | 2152.5 |
| 22.5° | 2097.9 |
| 25°   | 2028.5 |
| 27.5° | 1939.2 |
| 30°   | 1825.1 |
| 32.5° | 1706.1 |
| 35°   | 1562.3 |
| 37.5° | 1403.6 |
| 40°   | 1220.1 |
| 42.5° | 1036.6 |
| 45°   | 863.0  |
| 47.5° | 699.3  |
| 50°   | 555.5  |
| 52.5° | 421.6  |
| 55°   | 312.5  |
| 57.5° | 223.2  |
| 60°   | 153.7  |
| 62.5° | 114.1  |
| 65°   | 84.3   |
| 67.5° | 64.5   |
| 70°   | 44.6   |
| 72.5° | 34.7   |
| 75°   | 24.8   |
| 77.5° | 14.9   |
| 80°   | 9.9    |
| 82.5° | 5.0    |
| 85°   | 5.0    |
| 87.5° | 0.0    |
| 90°   | 0.0    |



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)