

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204403

Luminaire Tested: **LD6B40D010 EU6B30509040 6LBSGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204403
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B40D010 EU6B30509040 6LBSGPH1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH GRAPHITE HAZE TRIM
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57
W DL3-44.71 W DLE-39.33 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3463.7 lumens
Efficiency: N/A
Efficacy: 82.9 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.26
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204403

CATALOG NUMBER: LD6B40D010 EU6B30509040 6LBSGPH1

Luminous Intensity Polar Plot






TEST NUMBER: P204403

CATALOG NUMBER: LD6B40D010 EU6B30509040 6LBSGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	111	107	103	100		108	105	102	99		101	98	96		97	95	93		93	91	90
2	102	95	89	84		100	93	88	83		90	85	82		87	83	80		84	81	78
3	94	85	78	72		92	83	77	71		80	75	70		78	73	69		75	71	68
4	87	76	68	62		85	75	67	62		72	66	61		70	65	60		68	63	59
5	80	68	60	54		78	67	60	54		65	59	53		63	58	53		62	56	52
6	74	62	54	48		73	61	53	48		59	52	47		58	52	47		56	51	47
7	69	57	48	43		68	56	48	43		54	47	42		53	47	42		52	46	42
8	65	52	44	38		63	51	44	38		50	43	38		49	42	38		48	42	38
9	60	48	40	35		59	47	40	35		46	39	35		45	39	34		44	38	34
10	57	44	37	32		56	44	36	32		43	36	31		42	36	31		41	35	31

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204403

CATALOG NUMBER: LD6B40D010 EU6B30509040 6LBSGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	151.5	4.4
10°-20°	425.2	12.3
20°-30°	620.1	17.9
30°-40°	707.2	20.4
40°-50°	678.3	19.6
50°-60°	519.5	15.0
60°-70°	285.1	8.2
70°-80°	75.8	2.2
80°-90°	1.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1196.7	34.6
0°-40°	1903.9	55.0
0°-60°	3101.7	89.5
0°-90°	3463.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3463.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1609	
5°	1596	151
15°	1509	425
25°	1347	620
35°	1131	707
45°	881	678
55°	582	520
65°	287	285
75°	66	76
85°	0	1
90°	0	



TEST NUMBER: P204403

CATALOG NUMBER: LD6B40D010 EU6B30509040 6LBSGPH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	1608.7
2.5°	1604.6
5°	1596.3
7.5°	1583.8
10°	1567.2
12.5°	1538.1
15°	1509.0
17.5°	1475.7
20°	1438.3
22.5°	1392.6
25°	1346.8
27.5°	1301.1
30°	1242.9
32.5°	1188.9
35°	1130.7
37.5°	1072.5
40°	1014.3
42.5°	951.9
45°	881.3
47.5°	810.6
50°	735.8
52.5°	656.8
55°	582.0
57.5°	507.1
60°	428.2
62.5°	353.3
65°	286.8
67.5°	220.3
70°	162.1
72.5°	108.1
75°	66.5
77.5°	29.1
80°	8.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)