

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P202733

Luminaire Tested: **LD6B30D010 EU6B30508027 6LBWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P202733
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B30D010 EU6B30508027 6LBWH1
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W
DL3-29.67 W DLE-29.73 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2500.2 lumens
Efficiency: N/A
Efficacy: 89.3 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.16
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P202733

CATALOG NUMBER: LD6B30D010 EU6B30508027 6LBWH1

Luminous Intensity Polar Plot





TEST NUMBER: P202733

CATALOG NUMBER: LD6B30D010 EU6B30508027 6LBWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	101	103	100	98		99	97	95		95
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88
3	98	90	84	79	96	89	83	78	86	81	77		83	79	76		81
4	92	82	75	70	90	81	75	70	79	73	69		77	72	68		75
5	86	75	68	63	84	74	68	63	72	66	62		71	65	61		69
6	80	69	62	57	78	68	61	56	67	61	56		65	60	56		64
7	75	64	56	51	73	63	56	51	62	55	51		60	55	51		59
8	70	59	52	47	69	58	51	47	57	51	46		56	50	46		55
9	66	55	48	43	65	54	47	43	53	47	43		52	47	42		51
10	62	51	44	40	61	50	44	39	50	43	39		49	43	39		48

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P202733

CATALOG NUMBER: LD6B30D010 EU6B30508027 6LBWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	145.6	5.8
10°-20°	413.3	16.5
20°-30°	605.9	24.2
30°-40°	630.7	25.2
40°-50°	436.3	17.5
50°-60°	190.0	7.6
60°-70°	58.3	2.3
70°-80°	17.5	0.7
80°-90°	2.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1164.9	46.6
0°-40°	1795.5	71.8
0°-60°	2421.8	96.9
0°-90°	2500.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2500.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1542	
5°	1536	146
15°	1468	413
25°	1325	606
35°	1020	631
45°	564	436
55°	204	190
65°	55	58
75°	16	17
85°	3	3
90°	0	



TEST NUMBER: P202733

CATALOG NUMBER: LD6B30D010 EU6B30508027 6LBWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1542.1
2.5°	1545.3
5°	1535.6
7.5°	1522.7
10°	1506.5
12.5°	1490.3
15°	1467.6
17.5°	1438.4
20°	1406.0
22.5°	1370.4
25°	1325.0
27.5°	1266.7
30°	1192.2
32.5°	1114.5
35°	1020.5
37.5°	916.8
40°	797.0
42.5°	677.1
45°	563.7
47.5°	456.8
50°	362.8
52.5°	275.4
55°	204.1
57.5°	145.8
60°	100.4
62.5°	74.5
65°	55.1
67.5°	42.1
70°	29.2
72.5°	22.7
75°	16.2
77.5°	9.7
80°	6.5
82.5°	3.2
85°	3.2
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)