

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203583

Luminaire Tested: **LD6B50D010TE EU6B30508027 6LBMMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203583
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B50D010TE EU6B30508027 6LBMMW1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH MATTE WHITE TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4100.5 lumens
Efficiency: N/A
Efficacy: 69.8 lumens/watt
Spacing Criteria (0/90/45): 1 / 1 / 0.97
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 58.77
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203583

CATALOG NUMBER: LD6B50D010TE EU6B30508027 6LBMMW1

Luminous Intensity Polar Plot





TEST NUMBER: P203583

CATALOG NUMBER: LD6B50D010TE EU6B30508027 6LBMMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					0
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			0
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			100
1	111	108	104	101		109	105	103	100		101	99	97			98	96	94			89
2	104	97	92	88		101	96	91	87		92	88	85			89	86	83			79
3	97	88	82	77		95	87	81	76		84	79	75			82	77	74			71
4	90	81	74	68		88	80	73	68		77	72	67			75	70	66			64
5	85	74	67	61		83	73	66	61		71	65	61			69	64	60			58
6	79	68	61	56		78	68	61	56		66	60	55			64	59	55			53
7	75	63	56	51		73	63	56	51		61	55	50			60	54	50			48
8	70	59	52	47		69	58	51	47		57	51	46			56	50	46			44
9	66	55	48	43		65	54	48	43		53	47	43			52	47	43			41
10	63	51	45	40		62	51	44	40		50	44	40			49	44	40			38

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203583

CATALOG NUMBER: LD6B50D010TE EU6B30508027 6LBMMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	282.6	6.9
10°-20°	757.1	18.5
20°-30°	1016.5	24.8
30°-40°	833.9	20.3
40°-50°	500.7	12.2
50°-60°	332.8	8.1
60°-70°	223.0	5.4
70°-80°	120.0	2.9
80°-90°	33.8	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2056.2	50.1
0°-40°	2890.1	70.5
0°-60°	3723.6	90.8
0°-90°	4100.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4100.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3060	
5°	3009	283
15°	2698	757
25°	2240	1017
35°	1323	834
45°	633	501
55°	368	333
65°	226	223
75°	113	120
85°	28	34
90°	0	



TEST NUMBER: P203583

CATALOG NUMBER: LD6B50D010TE EU6B30508027 6LBMMW1

CANDELA DISTRIBUTION (FULL):

0°	
0°	3059.7
2.5°	3037.0
5°	3008.8
7.5°	2946.6
10°	2873.0
12.5°	2782.5
15°	2697.7
17.5°	2595.9
20°	2494.1
22.5°	2381.0
25°	2239.6
27.5°	2069.9
30°	1843.7
32.5°	1589.2
35°	1323.4
37.5°	1097.2
40°	904.9
42.5°	752.2
45°	633.4
47.5°	537.3
50°	469.4
52.5°	412.9
55°	367.6
57.5°	328.0
60°	294.1
62.5°	254.5
65°	226.2
67.5°	192.3
70°	164.0
72.5°	135.7
75°	113.1
77.5°	90.5
80°	67.9
82.5°	50.9
85°	28.3
87.5°	11.3
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)