

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204796

Luminaire Tested: **LD6B30D010 EU6B30508030 6LBCSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204796
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B30D010 EU6B30508030 6LBCSMW1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH CAST MATTE WHITE TRIM
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W
DL3-29.67 W DLE-29.73 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3245.7 lumens
Efficiency: N/A
Efficacy: 115.9 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204796

CATALOG NUMBER: LD6B30D010 EU6B30508030 6LBCSMW1

Luminous Intensity Polar Plot






TEST NUMBER: P204796

CATALOG NUMBER: LD6B30D010 EU6B30508030 6LBCSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	99	108	104	100	97	100	97	94		96	93	91		92
2	101	94	87	82	99	92	86	81	88	84	79		85	81	78		82
3	93	83	75	70	90	81	74	69	79	73	68		76	71	67		73
4	85	74	66	60	83	73	65	59	70	64	58		68	62	58		66
5	79	66	58	52	77	65	57	51	63	56	51		61	55	50		60
6	73	60	52	45	71	59	51	45	57	50	45		56	49	44		54
7	68	55	46	40	66	54	46	40	52	45	40		51	44	40		50
8	63	50	42	36	61	49	41	36	48	41	36		47	40	36		46
9	59	46	38	33	57	45	38	32	44	37	32		43	37	32		42
10	55	42	35	30	54	42	34	30	41	34	29		40	34	29		39

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204796

CATALOG NUMBER: LD6B30D010 EU6B30508030 6LBCSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	125.6	3.9
10°-20°	357.6	11.0
20°-30°	537.9	16.6
30°-40°	637.5	19.6
40°-50°	634.4	19.5
50°-60°	511.4	15.8
60°-70°	309.4	9.5
70°-80°	114.9	3.5
80°-90°	17.1	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1021.1	31.5
0°-40°	1658.5	51.1
0°-60°	2804.3	86.4
0°-90°	3245.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3245.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1326	
5°	1320	126
15°	1267	358
25°	1168	538
35°	1021	637
45°	826	634
55°	570	511
65°	311	309
75°	104	115
85°	14	17
90°	0	



TEST NUMBER: P204796

CATALOG NUMBER: LD6B30D010 EU6B30508030 6LBCSMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1325.6
2.5°	1325.6
5°	1319.7
7.5°	1315.8
10°	1304.0
12.5°	1284.3
15°	1266.6
17.5°	1247.0
20°	1223.4
22.5°	1199.8
25°	1168.3
27.5°	1134.8
30°	1097.5
32.5°	1062.1
35°	1020.8
37.5°	977.5
40°	926.4
42.5°	877.2
45°	826.1
47.5°	769.0
50°	706.1
52.5°	641.2
55°	570.4
57.5°	507.4
60°	436.6
62.5°	373.7
65°	310.8
67.5°	251.8
70°	196.7
72.5°	147.5
75°	104.2
77.5°	66.9
80°	39.3
82.5°	23.6
85°	13.8
87.5°	5.9
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)