

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203867

Luminaire Tested: **LD6B30D010 EU6B30508030 6LBNGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203867
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B30D010 EU6B30508030 6LBNGPH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH GRAPHITE HAZE TRIM
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W
DL3-29.67 W DLE-29.73 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1486.3 lumens
Efficiency: N/A
Efficacy: 53.1 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.88
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203867

CATALOG NUMBER: LD6B30D010 EU6B30508030 6LBNGPH1

Luminous Intensity Polar Plot






TEST NUMBER: P203867

CATALOG NUMBER: LD6B30D010 EU6B30508030 6LBNGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	100	98		97
2	108	103	99	96	106	101	98	95	98	95	93		95	93	91		92
3	103	96	91	87	101	95	90	87	92	88	85		90	87	84		88
4	97	90	84	80	96	89	84	80	87	82	79		85	81	78		83
5	93	84	78	74	91	83	78	74	82	77	73		80	76	73		78
6	88	79	73	69	86	78	73	69	77	72	68		75	71	68		74
7	84	74	68	64	82	74	68	64	72	67	64		71	67	63		70
8	79	70	64	60	78	69	64	60	68	63	60		67	63	59		66
9	76	66	60	56	75	66	60	56	65	60	56		64	59	56		63
10	72	63	57	53	71	62	57	53	61	56	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203867

CATALOG NUMBER: LD6B30D010 EU6B30508030 6LBNGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	163.5	11.0
10°-20°	403.3	27.1
20°-30°	488.7	32.9
30°-40°	333.0	22.4
40°-50°	79.3	5.3
50°-60°	12.4	0.8
60°-70°	4.6	0.3
70°-80°	1.3	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1055.6	71.0
0°-40°	1388.6	93.4
0°-60°	1480.3	99.6
0°-90°	1486.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1486.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1807	
5°	1756	164
15°	1444	403
25°	1068	489
35°	532	333
45°	85	79
55°	14	12
65°	3	5
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P203867

CATALOG NUMBER: LD6B30D010 EU6B30508030 6LBNGPH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1806.6
2.5°	1796.4
5°	1755.7
7.5°	1701.5
10°	1623.6
12.5°	1535.4
15°	1443.9
17.5°	1349.0
20°	1254.1
22.5°	1159.2
25°	1067.7
27.5°	982.9
30°	860.9
32.5°	701.6
35°	532.1
37.5°	379.6
40°	250.8
42.5°	155.9
45°	84.7
47.5°	44.1
50°	23.7
52.5°	16.9
55°	13.6
57.5°	10.2
60°	6.8
62.5°	6.8
65°	3.4
67.5°	3.4
70°	3.4
72.5°	3.4
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)