

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203764

Luminaire Tested: **LD6B30D010 EU6B30508030 6LBNWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203764
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B30D010 EU6B30508030 6LBNWH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W
DL3-29.67 W DLE-29.73 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1990.8 lumens
Efficiency: N/A
Efficacy: 71.1 lumens/watt
Spacing Criteria (0/90/45): 0.56 / 0.56 / 0.64
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203764

CATALOG NUMBER: LD6B30D010 EU6B30508030 6LBNWH1

Luminous Intensity Polar Plot





TEST NUMBER: P203764

CATALOG NUMBER: LD6B30D010 EU6B30508030 6LBNWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			0
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			100
1	114	111	109	107	112	109	107	105		105	104	102			101	100	99			94
2	109	104	101	97	107	103	99	96		99	97	94			96	94	92			89
3	104	98	93	90	102	97	92	89		94	91	88			92	89	86			83
4	99	92	87	83	97	91	86	83		89	85	82			87	84	81			79
5	95	87	82	78	93	86	81	77		84	80	77			83	79	76			74
6	91	82	77	73	89	82	76	73		80	76	72			79	75	72			70
7	87	78	73	69	85	77	72	69		76	72	68			75	71	68			66
8	83	74	69	65	82	74	68	65		73	68	65			72	67	64			63
9	79	71	65	62	78	70	65	61		69	65	61			68	64	61			60
10	76	67	62	58	75	67	62	58		66	61	58			65	61	58			57

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203764

CATALOG NUMBER: LD6B30D010 EU6B30508030 6LBNWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	330.9	16.6
10°-20°	635.7	31.9
20°-30°	578.0	29.0
30°-40°	350.3	17.6
40°-50°	79.8	4.0
50°-60°	10.2	0.5
60°-70°	4.6	0.2
70°-80°	1.3	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1544.5	77.6
0°-40°	1894.9	95.2
0°-60°	1984.8	99.7
0°-90°	1990.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1990.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3908	
5°	3685	331
15°	2290	636
25°	1253	578
35°	555	350
45°	88	80
55°	10	10
65°	3	5
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P203764

CATALOG NUMBER: LD6B30D010 EU6B30508030 6LBNWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	3908.4
2.5°	3861.0
5°	3684.9
7.5°	3400.4
10°	3038.0
12.5°	2662.0
15°	2289.5
17.5°	1950.8
20°	1666.3
22.5°	1436.0
25°	1253.1
27.5°	1090.6
30°	931.4
32.5°	745.1
35°	555.4
37.5°	389.5
40°	257.4
42.5°	159.2
45°	88.1
47.5°	40.6
50°	16.9
52.5°	13.5
55°	10.2
57.5°	10.2
60°	6.8
62.5°	6.8
65°	3.4
67.5°	3.4
70°	3.4
72.5°	3.4
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)