

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203074

Luminaire Tested: **LD6B50D010TE EU6B30509027 6LBWB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203074
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B50D010TE EU6B30509027 6LBWB1
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH SPECULAR BLACK TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2469.7 lumens
Efficiency: N/A
Efficacy: 42.0 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.08 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 58.77
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203074

CATALOG NUMBER: LD6B50D010TE EU6B30509027 6LBWB1

Luminous Intensity Polar Plot






TEST NUMBER: P203074

CATALOG NUMBER: LD6B50D010TE EU6B30509027 6LBWB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		96
2	106	101	97	93	104	99	95	92	96	93	90		93	90	88		90
3	100	93	87	83	98	92	86	82	89	85	81		86	83	80		84
4	94	86	79	75	92	85	79	74	82	77	73		80	76	73		78
5	89	79	73	68	87	78	72	67	76	71	67		75	70	66		73
6	83	73	67	62	82	72	66	61	71	65	61		69	64	61		68
7	78	68	61	56	77	67	61	56	66	60	56		65	60	56		63
8	74	63	57	52	73	63	56	52	61	56	52		60	55	51		59
9	70	59	52	48	69	58	52	48	57	52	48		57	51	47		56
10	66	55	49	44	65	55	49	44	54	48	44		53	48	44		52

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203074

CATALOG NUMBER: LD6B50D010TE EU6B30509027 6LBWB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	175.0	7.1
10°-20°	489.4	19.8
20°-30°	685.5	27.8
30°-40°	654.7	26.5
40°-50°	372.8	15.1
50°-60°	91.1	3.7
60°-70°	1.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1349.9	54.7
0°-40°	2004.6	81.2
0°-60°	2468.5	100.0
0°-90°	2469.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2469.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1861	
5°	1846	175
15°	1736	489
25°	1499	686
35°	1066	655
45°	478	373
55°	91	91
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P203074

CATALOG NUMBER: LD6B50D010TE EU6B30509027 6LBWB1

CANDELA DISTRIBUTION (FULL):

0°	
0°	1861.3
2.5°	1861.3
5°	1846.3
7.5°	1826.1
10°	1811.0
12.5°	1780.9
15°	1735.6
17.5°	1695.3
20°	1645.0
22.5°	1579.6
25°	1499.1
27.5°	1408.6
30°	1308.0
32.5°	1187.2
35°	1066.5
37.5°	920.6
40°	764.7
42.5°	618.8
45°	477.9
47.5°	352.1
50°	246.5
52.5°	156.0
55°	90.6
57.5°	40.2
60°	10.1
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)