

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204279

Luminaire Tested: **LD6B30D010 EU6B30508030 6LBSWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204279
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B30D010 EU6B30508030 6LBSWH1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W
DL3-29.67 W DLE-29.73 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3094.4 lumens
Efficiency: N/A
Efficacy: 110.5 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204279

CATALOG NUMBER: LD6B30D010 EU6B30508030 6LBSWH1

Luminous Intensity Polar Plot





TEST NUMBER: P204279

CATALOG NUMBER: LD6B30D010 EU6B30508030 6LBSWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	111	107	104	101	108	105	102	99		101	98	96		97	95	93		94	92	90
2	103	96	90	85	100	94	89	84		91	86	83		87	84	81		85	82	79
3	95	86	79	73	93	84	78	73		82	76	72		79	74	70		76	73	69
4	88	77	70	64	86	76	69	63		74	68	63		72	66	62		69	65	61
5	81	70	62	56	79	69	62	56		67	60	55		65	59	55		63	58	54
6	76	64	56	50	74	63	55	50		61	54	49		60	54	49		58	53	49
7	71	58	51	45	69	58	50	45		56	49	45		55	49	44		54	48	44
8	66	54	46	41	65	53	46	41		52	45	40		51	45	40		50	44	40
9	62	50	42	37	61	49	42	37		48	41	37		47	41	37		46	41	37
10	58	46	39	34	57	46	39	34		45	38	34		44	38	34		43	38	34

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204279

CATALOG NUMBER: LD6B30D010 EU6B30508030 6LBSWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	170.2	5.5
10°-20°	440.6	14.2
20°-30°	576.3	18.6
30°-40°	610.2	19.7
40°-50°	569.1	18.4
50°-60°	431.0	13.9
60°-70°	233.5	7.5
70°-80°	62.6	2.0
80°-90°	0.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1187.0	38.4
0°-40°	1797.2	58.1
0°-60°	2797.4	90.4
0°-90°	3094.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3094.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1846	
5°	1818	170
15°	1575	441
25°	1253	576
35°	975	610
45°	742	569
55°	484	431
65°	234	233
75°	54	63
85°	0	1
90°	0	



TEST NUMBER: P204279

CATALOG NUMBER: LD6B30D010 EU6B30508030 6LBSWH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	1845.5
2.5°	1838.7
5°	1818.4
7.5°	1774.4
10°	1716.8
12.5°	1649.1
15°	1574.6
17.5°	1489.9
20°	1415.4
22.5°	1330.8
25°	1252.9
27.5°	1175.0
30°	1100.5
32.5°	1036.2
35°	975.2
37.5°	914.3
40°	856.7
42.5°	799.1
45°	741.6
47.5°	677.2
50°	612.9
52.5°	548.6
55°	484.2
57.5°	416.5
60°	352.2
62.5°	291.2
65°	233.6
67.5°	179.5
70°	132.1
72.5°	91.4
75°	54.2
77.5°	23.7
80°	6.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)