

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P202734

Luminaire Tested: **LD6B30D010 EU6B30508030 6LBWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P202734
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B30D010 EU6B30508030 6LBWH1
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W
DL3-29.67 W DLE-29.73 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2613.7 lumens
Efficiency: N/A
Efficacy: 93.3 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.16
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P202734

CATALOG NUMBER: LD6B30D010 EU6B30508030 6LBWH1

Luminous Intensity Polar Plot





TEST NUMBER: P202734

CATALOG NUMBER: LD6B30D010 EU6B30508030 6LBWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	101	103	100	98		99	97	95		95
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88
3	98	90	84	79	96	89	83	78	86	81	77		83	79	76		81
4	92	82	75	70	90	81	75	70	79	73	69		77	72	68		75
5	86	75	68	63	84	74	68	63	72	66	62		71	65	61		69
6	80	69	62	57	78	68	61	56	67	61	56		65	60	56		64
7	75	64	56	51	73	63	56	51	62	55	51		60	55	51		59
8	70	59	52	47	69	58	51	47	57	51	46		56	50	46		55
9	66	55	48	43	65	54	47	43	53	47	43		52	47	42		51
10	62	51	44	40	61	50	44	39	50	43	39		49	43	39		48

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P202734

CATALOG NUMBER: LD6B30D010 EU6B30508030 6LBWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	152.3	5.8
10°-20°	432.0	16.5
20°-30°	633.5	24.2
30°-40°	659.3	25.2
40°-50°	456.1	17.5
50°-60°	198.6	7.6
60°-70°	60.9	2.3
70°-80°	18.3	0.7
80°-90°	2.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1217.8	46.6
0°-40°	1877.0	71.8
0°-60°	2531.7	96.9
0°-90°	2613.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2613.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1612	
5°	1605	152
15°	1534	432
25°	1385	633
35°	1067	659
45°	589	456
55°	213	199
65°	58	61
75°	17	18
85°	3	3
90°	0	



TEST NUMBER: P202734

CATALOG NUMBER: LD6B30D010 EU6B30508030 6LBWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1612.1
2.5°	1615.5
5°	1605.3
7.5°	1591.8
10°	1574.8
12.5°	1557.9
15°	1534.2
17.5°	1503.7
20°	1469.8
22.5°	1432.6
25°	1385.2
27.5°	1324.2
30°	1246.3
32.5°	1165.0
35°	1066.8
37.5°	958.4
40°	833.1
42.5°	707.8
45°	589.3
47.5°	477.5
50°	379.3
52.5°	287.9
55°	213.4
57.5°	152.4
60°	105.0
62.5°	77.9
65°	57.6
67.5°	44.0
70°	30.5
72.5°	23.7
75°	16.9
77.5°	10.2
80°	6.8
82.5°	3.4
85°	3.4
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)