

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205234

Luminaire Tested: **LD6B50D010TE EU6B30509027 6LBWLI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205234
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B50D010TE EU6B30509027 6LBWL11
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH SPECULAR CLEAR TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4436.5 lumens
Efficiency: N/A
Efficacy: 75.5 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.18
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 58.77
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205234

CATALOG NUMBER: LD6B50D010TE EU6B30509027 6LBWLI1

Luminous Intensity Polar Plot




TEST NUMBER: P205234
CATALOG NUMBER: LD6B50D010TE EU6B30509027 6LBWLI1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	104	110	107	105	103	103	101	99		100	98	97		96
2	106	101	96	92	104	99	95	91	95	92	89		92	90	87		90
3	100	92	87	82	97	91	86	81	88	84	80		86	82	79		83
4	93	85	78	73	92	84	78	73	81	76	72		79	75	71		77
5	88	78	71	66	86	77	71	66	75	70	65		73	69	65		72
6	82	72	65	60	81	71	65	60	70	64	59		68	63	59		67
7	77	67	60	55	76	66	59	55	65	59	54		63	58	54		62
8	73	62	55	50	71	61	55	50	60	54	50		59	54	50		58
9	69	57	51	46	67	57	50	46	56	50	46		55	50	46		54
10	65	54	47	43	64	53	47	42	52	46	42		51	46	42		51

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205234

CATALOG NUMBER: LD6B50D010TE EU6B30509027 6LBWLI1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	267.4	6.0
10°-20°	803.6	18.1
20°-30°	1211.4	27.3
30°-40°	1239.9	27.9
40°-50°	722.4	16.3
50°-60°	166.0	3.7
60°-70°	20.4	0.5
70°-80°	5.3	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2282.5	51.4
0°-40°	3522.4	79.4
0°-60°	4410.8	99.4
0°-90°	4436.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4436.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2772	
5°	2787	267
15°	2847	804
25°	2656	1211
35°	2012	1240
45°	931	722
55°	161	166
65°	15	20
75°	5	5
85°	0	0
90°	0	



TEST NUMBER: P205234

CATALOG NUMBER: LD6B50D010TE EU6B30509027 6LBWLI1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2771.5
2.5°	2766.5
5°	2786.6
7.5°	2806.7
10°	2831.9
12.5°	2836.9
15°	2847.0
17.5°	2836.9
20°	2811.8
22.5°	2731.3
25°	2655.8
27.5°	2535.1
30°	2379.2
32.5°	2218.2
35°	2012.0
37.5°	1780.6
40°	1524.1
42.5°	1237.4
45°	930.6
47.5°	648.9
50°	427.6
52.5°	271.6
55°	161.0
57.5°	85.5
60°	45.3
62.5°	25.2
65°	15.1
67.5°	15.1
70°	10.1
72.5°	5.0
75°	5.0
77.5°	5.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)