

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205204

Luminaire Tested: **LD6B30D010 EU6B30508030 6LBWLI1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P205204  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD6B30D010 EU6B30508030 6LBWLI1  
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT  
WIDE DISTRIBUTION WITH SPECULAR CLEAR TRIM  
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W  
DL3-29.67 W DLE-29.73 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2986.1 lumens  
Efficiency: N/A  
Efficacy: 106.6 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.18  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P205204

CATALOG NUMBER: LD6B30D010 EU6B30508030 6LBWLI1

### Luminous Intensity Polar Plot





TEST NUMBER: P205204

CATALOG NUMBER: LD6B30D010 EU6B30508030 6LBWLI1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 113 | 110 | 107 | 104 | 110 | 107 | 105 | 103 | 103 | 101 | 99  |  | 100 | 98  | 97  |  | 96  |
| 2   | 106 | 101 | 96  | 92  | 104 | 99  | 95  | 91  | 95  | 92  | 89  |  | 92  | 90  | 87  |  | 90  |
| 3   | 100 | 92  | 87  | 82  | 97  | 91  | 86  | 81  | 88  | 84  | 80  |  | 86  | 82  | 79  |  | 83  |
| 4   | 93  | 85  | 78  | 73  | 92  | 84  | 78  | 73  | 81  | 76  | 72  |  | 79  | 75  | 71  |  | 77  |
| 5   | 88  | 78  | 71  | 66  | 86  | 77  | 71  | 66  | 75  | 70  | 65  |  | 73  | 69  | 65  |  | 72  |
| 6   | 82  | 72  | 65  | 60  | 81  | 71  | 65  | 60  | 70  | 64  | 59  |  | 68  | 63  | 59  |  | 67  |
| 7   | 77  | 67  | 60  | 55  | 76  | 66  | 59  | 55  | 65  | 59  | 54  |  | 63  | 58  | 54  |  | 62  |
| 8   | 73  | 62  | 55  | 50  | 71  | 61  | 55  | 50  | 60  | 54  | 50  |  | 59  | 54  | 50  |  | 58  |
| 9   | 69  | 57  | 51  | 46  | 67  | 57  | 50  | 46  | 56  | 50  | 46  |  | 55  | 50  | 46  |  | 54  |
| 10  | 65  | 54  | 47  | 43  | 64  | 53  | 47  | 42  | 52  | 46  | 42  |  | 51  | 46  | 42  |  | 51  |

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P205204

CATALOG NUMBER: LD6B30D010 EU6B30508030 6LBWLI1

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 180.0  | 6.0       |
| 10°-20°   | 540.9  | 18.1      |
| 20°-30°   | 815.4  | 27.3      |
| 30°-40°   | 834.6  | 27.9      |
| 40°-50°   | 486.2  | 16.3      |
| 50°-60°   | 111.7  | 3.7       |
| 60°-70°   | 13.8   | 0.5       |
| 70°-80°   | 3.6    | 0.1       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 1536.3 | 51.4      |
| 0°-40°    | 2370.8 | 79.4      |
| 0°-60°    | 2968.8 | 99.4      |
| 0°-90°    | 2986.1 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 2986.1 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 1866 |      |
| 5°  | 1876 | 180  |
| 15° | 1916 | 541  |
| 25° | 1788 | 815  |
| 35° | 1354 | 835  |
| 45° | 626  | 486  |
| 55° | 108  | 112  |
| 65° | 10   | 14   |
| 75° | 3    | 4    |
| 85° | 0    | 0    |
| 90° | 0    |      |



TEST NUMBER: P205204

CATALOG NUMBER: LD6B30D010 EU6B30508030 6LBWLI1

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     |
|-------|--------|
| 0°    | 1865.5 |
| 2.5°  | 1862.1 |
| 5°    | 1875.6 |
| 7.5°  | 1889.2 |
| 10°   | 1906.1 |
| 12.5° | 1909.5 |
| 15°   | 1916.2 |
| 17.5° | 1909.5 |
| 20°   | 1892.5 |
| 22.5° | 1838.4 |
| 25°   | 1787.6 |
| 27.5° | 1706.3 |
| 30°   | 1601.4 |
| 32.5° | 1493.0 |
| 35°   | 1354.2 |
| 37.5° | 1198.5 |
| 40°   | 1025.8 |
| 42.5° | 832.9  |
| 45°   | 626.3  |
| 47.5° | 436.7  |
| 50°   | 287.8  |
| 52.5° | 182.8  |
| 55°   | 108.3  |
| 57.5° | 57.6   |
| 60°   | 30.5   |
| 62.5° | 16.9   |
| 65°   | 10.2   |
| 67.5° | 10.2   |
| 70°   | 6.8    |
| 72.5° | 3.4    |
| 75°   | 3.4    |
| 77.5° | 3.4    |
| 80°   | 0.0    |
| 82.5° | 0.0    |
| 85°   | 0.0    |
| 87.5° | 0.0    |
| 90°   | 0.0    |



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)