

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203146

Luminaire Tested: **LD6B30D010 EU6B30508030 6LBWMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203146
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B30D010 EU6B30508030 6LBWMW1
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W
DL3-29.67 W DLE-29.73 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2793.1 lumens
Efficiency: N/A
Efficacy: 99.8 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 1.13 / 1.15
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203146

CATALOG NUMBER: LD6B30D010 EU6B30508030 6LBWMW1

Luminous Intensity Polar Plot






TEST NUMBER: P203146

CATALOG NUMBER: LD6B30D010 EU6B30508030 6LBWMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	111	107	104	100		108	105	102	99		101	98	96		97	95	93		93	92	90
2	103	96	90	86		100	94	89	85		91	86	83		88	84	81		85	82	79
3	95	86	80	74		93	85	79	74		82	77	72		80	75	71		77	73	70
4	89	78	71	65		86	77	70	65		75	69	64		72	67	63		70	66	62
5	82	71	64	58		80	70	63	58		68	62	57		66	61	56		65	60	56
6	77	65	57	52		75	64	57	52		63	56	51		61	55	51		60	54	50
7	72	60	52	47		70	59	52	47		58	51	46		56	50	46		55	50	46
8	67	55	48	42		66	55	47	42		53	47	42		52	46	42		51	46	42
9	63	51	44	39		62	51	44	39		50	43	39		49	43	38		48	42	38
10	60	48	40	36		58	47	40	36		46	40	36		45	40	35		45	39	35

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203146

CATALOG NUMBER: LD6B30D010 EU6B30508030 6LBWMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	147.7	5.3
10°-20°	414.3	14.8
20°-30°	596.9	21.4
30°-40°	619.7	22.2
40°-50°	458.2	16.4
50°-60°	273.7	9.8
60°-70°	166.3	6.0
70°-80°	91.1	3.3
80°-90°	25.4	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1158.8	41.5
0°-40°	1778.5	63.7
0°-60°	2510.4	89.9
0°-90°	2793.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2793.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1568	
5°	1558	148
15°	1470	414
25°	1301	597
35°	999	620
45°	590	458
55°	298	274
65°	166	166
75°	85	91
85°	20	25
90°	0	



TEST NUMBER: P203146

CATALOG NUMBER: LD6B30D010 EU6B30508030 6LBWMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1568.5
2.5°	1568.5
5°	1558.3
7.5°	1544.8
10°	1524.5
12.5°	1500.7
15°	1470.3
17.5°	1436.4
20°	1402.5
22.5°	1355.1
25°	1300.9
27.5°	1243.3
30°	1168.8
32.5°	1094.2
35°	999.4
37.5°	901.1
40°	792.7
42.5°	687.7
45°	589.5
47.5°	501.4
50°	423.5
52.5°	355.7
55°	298.1
57.5°	254.1
60°	216.8
62.5°	189.7
65°	166.0
67.5°	145.7
70°	125.3
72.5°	105.0
75°	84.7
77.5°	67.8
80°	50.8
82.5°	37.3
85°	20.3
87.5°	10.2
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)