

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204699

Luminaire Tested: **LD6B30D010 EU6B30509030 6LBPSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204699
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B30D010 EU6B30509030 6LBPSMW1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH PLASTIC MATTE WHITE TRIM
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W
DL3-29.67 W DLE-29.73 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2741.0 lumens
Efficiency: N/A
Efficacy: 97.9 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204699

CATALOG NUMBER: LD6B30D010 EU6B30509030 6LBPSMW1

Luminous Intensity Polar Plot






TEST NUMBER: P204699

CATALOG NUMBER: LD6B30D010 EU6B30509030 6LBPSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	99	107	104	100	97	99	97	94		96	93	91		92
2	101	93	87	82	98	92	86	81	88	83	79		85	81	77		82
3	93	83	75	69	90	81	74	69	78	72	67		76	70	66		73
4	85	74	66	59	83	72	65	59	70	63	58		68	62	57		66
5	78	66	58	51	76	65	57	51	63	56	51		61	55	50		59
6	73	60	51	45	71	59	51	45	57	50	44		55	49	44		54
7	67	54	46	40	66	54	46	40	52	45	40		51	44	39		49
8	63	50	41	36	61	49	41	36	48	41	35		46	40	35		45
9	59	46	38	32	57	45	37	32	44	37	32		43	36	32		42
10	55	42	34	29	54	42	34	29	41	34	29		40	33	29		39

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204699

CATALOG NUMBER: LD6B30D010 EU6B30509030 6LBPSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	104.6	3.8
10°-20°	298.3	10.9
20°-30°	449.2	16.4
30°-40°	534.5	19.5
40°-50°	533.5	19.5
50°-60°	433.9	15.8
60°-70°	266.9	9.7
70°-80°	103.4	3.8
80°-90°	16.6	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	852.1	31.1
0°-40°	1386.6	50.6
0°-60°	2354.1	85.9
0°-90°	2741.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2741.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1104	
5°	1101	105
15°	1059	298
25°	978	449
35°	856	535
45°	694	534
55°	486	434
65°	268	267
75°	94	103
85°	13	17
90°	0	



TEST NUMBER: P204699

CATALOG NUMBER: LD6B30D010 EU6B30509030 6LBPSMW1

CANDELA DISTRIBUTION (FULL):

0°	
0°	1104.3
2.5°	1106.0
5°	1101.1
7.5°	1094.6
10°	1086.5
12.5°	1071.9
15°	1058.9
17.5°	1039.4
20°	1018.3
22.5°	998.8
25°	977.7
27.5°	948.4
30°	919.2
32.5°	891.6
35°	855.9
37.5°	816.9
40°	781.2
42.5°	737.3
45°	693.5
47.5°	646.4
50°	596.0
52.5°	544.0
55°	485.6
57.5°	428.7
60°	373.5
62.5°	319.9
65°	268.0
67.5°	219.2
70°	173.8
72.5°	131.5
75°	94.2
77.5°	61.7
80°	37.4
82.5°	22.7
85°	13.0
87.5°	6.5
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)