

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P202667

Luminaire Tested: **LD6B50D010TE EU6B30509727 6LBMWMH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P202667
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B50D010TE EU6B30509727 6LBMWMH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH WARM HAZE TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2995.1 lumens
Efficiency: N/A
Efficacy: 51.0 lumens/watt
Spacing Criteria (0/90/45): 0.9 / 0.9 / 0.89
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 58.77
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P202667

CATALOG NUMBER: LD6B50D010TE EU6B30509727 6LBMWMH1

Luminous Intensity Polar Plot





TEST NUMBER: P202667

CATALOG NUMBER: LD6B50D010TE EU6B30509727 6LBMWMH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			0
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			100
1	113	111	108	106	111	108	106	104		104	103	101			101	99	98			93
2	108	103	99	95	105	101	97	94		98	95	92			95	92	90			86
3	102	95	90	86	100	94	89	86		91	88	84			89	86	83			80
4	97	89	83	79	95	88	83	79		86	81	78			84	80	77			74
5	92	83	77	73	90	82	77	73		80	76	72			79	75	71			69
6	87	78	72	67	85	77	71	67		76	71	67			74	70	66			64
7	83	73	67	63	81	72	67	63		71	66	62			70	65	62			60
8	78	69	63	58	77	68	62	58		67	62	58			66	61	58			56
9	75	65	59	55	73	64	59	55		63	58	54			62	58	54			53
10	71	61	55	51	70	61	55	51		60	55	51			59	54	51			50

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P202667

CATALOG NUMBER: LD6B50D010TE EU6B30509727 6LBMWMH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	305.7	10.2
10°-20°	784.8	26.2
20°-30°	963.9	32.2
30°-40°	660.9	22.1
40°-50°	212.5	7.1
50°-60°	43.0	1.4
60°-70°	16.9	0.6
70°-80°	6.4	0.2
80°-90°	1.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2054.4	68.6
0°-40°	2715.3	90.7
0°-60°	2970.8	99.2
0°-90°	2995.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2995.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3331	
5°	3267	306
15°	2807	785
25°	2126	964
35°	1054	661
45°	252	212
55°	43	43
65°	18	17
75°	5	6
85°	0	1
90°	0	



TEST NUMBER: P202667

CATALOG NUMBER: LD6B50D010TE EU6B30509727 6LBMWMH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	3330.8
2.5°	3310.5
5°	3267.3
7.5°	3186.0
10°	3076.7
12.5°	2942.1
15°	2807.4
17.5°	2657.5
20°	2492.4
22.5°	2319.6
25°	2126.5
27.5°	1913.1
30°	1643.8
32.5°	1346.6
35°	1054.4
37.5°	787.6
40°	566.6
42.5°	386.2
45°	251.5
47.5°	155.0
50°	94.0
52.5°	58.4
55°	43.2
57.5°	33.0
60°	25.4
62.5°	20.3
65°	17.8
67.5°	12.7
70°	10.2
72.5°	7.6
75°	5.1
77.5°	5.1
80°	2.5
82.5°	2.5
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)