

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204910

Luminaire Tested: **LD6B30D010 EU6B30509730 6LBCSMB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204910
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B30D010 EU6B30509730 6LBCSMB1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH CAST MATTE BLACK TRIM
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W
DL3-29.67 W DLE-29.73 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2047.3 lumens
Efficiency: N/A
Efficacy: 73.1 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204910

CATALOG NUMBER: LD6B30D010 EU6B30509730 6LBCSMB1

Luminous Intensity Polar Plot





TEST NUMBER: P204910

CATALOG NUMBER: LD6B30D010 EU6B30509730 6LBCSMB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	107	103	100	108	104	101	98	100	98	95	96	94	92	93	91	90	88		
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77	75		
3	93	84	77	71	91	83	76	70	80	74	69	77	72	68	74	70	67	65		
4	86	75	67	61	84	74	66	61	71	65	60	69	63	59	67	62	58	56		
5	79	67	59	53	77	66	59	53	64	57	52	62	56	52	61	55	51	49		
6	74	61	53	47	72	60	52	46	58	51	46	57	50	46	55	50	45	43		
7	68	55	47	41	67	55	47	41	53	46	41	52	45	41	50	45	40	39		
8	64	51	43	37	62	50	42	37	49	42	37	48	41	37	46	41	36	35		
9	60	47	39	33	58	46	39	33	45	38	33	44	38	33	43	37	33	31		
10	56	43	35	30	55	43	35	30	42	35	30	41	34	30	40	34	30	28		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204910

CATALOG NUMBER: LD6B30D010 EU6B30509730 6LBCSMB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	81.8	4.0
10°-20°	232.9	11.4
20°-30°	350.2	17.1
30°-40°	415.5	20.3
40°-50°	411.2	20.1
50°-60°	323.0	15.8
60°-70°	181.1	8.8
70°-80°	50.8	2.5
80°-90°	0.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	664.9	32.5
0°-40°	1080.4	52.8
0°-60°	1814.5	88.6
0°-90°	2047.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2047.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	864	
5°	863	82
15°	826	233
25°	760	350
35°	666	415
45°	536	411
55°	364	323
65°	180	181
75°	44	51
85°	0	1
90°	0	



TEST NUMBER: P204910

CATALOG NUMBER: LD6B30D010 EU6B30509730 6LBCSMB1

CANDELA DISTRIBUTION (FULL):

	0°
0°	864.5
2.5°	861.5
5°	863.0
7.5°	855.6
10°	846.8
12.5°	836.6
15°	826.3
17.5°	813.1
20°	795.5
22.5°	777.9
25°	760.2
27.5°	741.2
30°	716.2
32.5°	691.3
35°	666.3
37.5°	637.0
40°	603.2
42.5°	570.9
45°	535.7
47.5°	496.1
50°	455.0
52.5°	408.0
55°	364.0
57.5°	314.1
60°	267.1
62.5°	224.6
65°	180.5
67.5°	142.4
70°	105.7
72.5°	71.9
75°	44.0
77.5°	22.0
80°	5.9
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)