

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204511

Luminaire Tested: **LD6B50D010TE EU6B30508030 6LBSB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204511
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B50D010TE EU6B30508030 6LBSB1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH SPECULAR BLACK TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4892.9 lumens
Efficiency: N/A
Efficacy: 83.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.3
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 58.77
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204511

CATALOG NUMBER: LD6B50D010TE EU6B30508030 6LBSB1

Luminous Intensity Polar Plot





TEST NUMBER: P204511

CATALOG NUMBER: LD6B50D010TE EU6B30508030 6LBSB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	107	103	100	108	105	101	98	100	98	95	97	94	93	93	91	90	88		
2	102	95	89	84	100	93	88	83	90	85	81	86	83	79	84	80	78	76		
3	94	84	77	72	91	83	76	71	80	74	70	77	73	68	75	71	67	65		
4	86	76	68	62	84	74	67	61	72	65	60	70	64	60	68	63	59	57		
5	80	68	60	54	78	67	59	53	65	58	53	63	57	52	61	56	52	50		
6	74	62	53	47	72	61	53	47	59	52	47	57	51	46	56	50	46	44		
7	69	56	48	42	67	55	48	42	54	47	42	52	46	41	51	45	41	39		
8	64	51	43	38	63	51	43	38	49	42	37	48	42	37	47	41	37	35		
9	60	47	39	34	59	47	39	34	46	39	34	45	38	34	44	38	34	32		
10	56	44	36	31	55	43	36	31	42	36	31	41	35	31	40	35	31	29		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204511

CATALOG NUMBER: LD6B50D010TE EU6B30508030 6LBSB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	203.7	4.2
10°-20°	578.0	11.8
20°-30°	859.8	17.6
30°-40°	1000.6	20.4
40°-50°	975.3	19.9
50°-60°	750.1	15.3
60°-70°	414.7	8.5
70°-80°	109.8	2.2
80°-90°	0.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1641.6	33.6
0°-40°	2642.2	54.0
0°-60°	4367.6	89.3
0°-90°	4892.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4892.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2158	
5°	2146	204
15°	2047	578
25°	1867	860
35°	1606	1001
45°	1265	975
55°	837	750
65°	416	415
75°	93	110
85°	0	1
90°	0	



TEST NUMBER: P204511

CATALOG NUMBER: LD6B50D010TE EU6B30508030 6LBSB1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2158.4
2.5°	2158.4
5°	2146.0
7.5°	2127.4
10°	2115.0
12.5°	2077.8
15°	2046.8
17.5°	2015.8
20°	1972.4
22.5°	1928.9
25°	1866.9
27.5°	1804.9
30°	1742.9
32.5°	1674.6
35°	1606.4
37.5°	1519.6
40°	1445.2
42.5°	1364.5
45°	1265.3
47.5°	1172.3
50°	1066.8
52.5°	955.2
55°	837.3
57.5°	725.7
60°	620.2
62.5°	514.8
65°	415.6
67.5°	322.5
70°	235.7
72.5°	161.3
75°	93.0
77.5°	43.4
80°	6.2
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)