

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204290

Luminaire Tested: **LD6B30D010 EU6B30509730 6LBSWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204290
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B30D010 EU6B30509730 6LBSWH1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W
DL3-29.67 W DLE-29.73 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2310.0 lumens
Efficiency: N/A
Efficacy: 82.5 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204290

CATALOG NUMBER: LD6B30D010 EU6B30509730 6LBSWH1

Luminous Intensity Polar Plot





TEST NUMBER: P204290

CATALOG NUMBER: LD6B30D010 EU6B30509730 6LBSWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			50
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			102
1	111	107	104	101	108	105	102	99		101	98	96			97	95	93			94
2	103	96	90	85	100	94	89	84		91	86	83			87	84	81			85
3	95	86	79	73	93	84	78	73		82	76	72			79	74	70			76
4	88	77	70	64	86	76	69	63		74	68	63			72	66	62			69
5	81	70	62	56	79	69	62	56		67	60	55			65	59	55			63
6	76	64	56	50	74	63	55	50		61	54	49			60	54	49			58
7	71	58	51	45	69	58	50	45		56	49	45			55	49	44			54
8	66	54	46	41	65	53	46	41		52	45	40			51	45	40			50
9	62	50	42	37	61	49	42	37		48	41	37			47	41	37			46
10	58	46	39	34	57	46	39	34		45	38	34			44	38	34			43

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204290

CATALOG NUMBER: LD6B30D010 EU6B30509730 6LBSWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	127.1	5.5
10°-20°	328.9	14.2
20°-30°	430.2	18.6
30°-40°	455.5	19.7
40°-50°	424.9	18.4
50°-60°	321.8	13.9
60°-70°	174.3	7.5
70°-80°	46.8	2.0
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	886.1	38.4
0°-40°	1341.6	58.1
0°-60°	2088.2	90.4
0°-90°	2310.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2310.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1378	
5°	1357	127
15°	1175	329
25°	935	430
35°	728	455
45°	554	425
55°	362	322
65°	174	174
75°	40	47
85°	0	1
90°	0	



TEST NUMBER: P204290

CATALOG NUMBER: LD6B30D010 EU6B30509730 6LBSWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1377.7
2.5°	1372.6
5°	1357.4
7.5°	1324.6
10°	1281.6
12.5°	1231.0
15°	1175.4
17.5°	1112.2
20°	1056.6
22.5°	993.4
25°	935.3
27.5°	877.2
30°	821.5
32.5°	773.5
35°	728.0
37.5°	682.5
40°	639.5
42.5°	596.6
45°	553.6
47.5°	505.6
50°	457.5
52.5°	409.5
55°	361.5
57.5°	310.9
60°	262.9
62.5°	217.4
65°	174.4
67.5°	134.0
70°	98.6
72.5°	68.3
75°	40.4
77.5°	17.7
80°	5.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)