

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P202539

Luminaire Tested: **LD6B30D010 EU6B30509730 6LBSWMH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P202539
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B30D010 EU6B30509730 6LBSWMH1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH WARM HAZE TRIM
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W
DL3-29.67 W DLE-29.73 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2318.3 lumens
Efficiency: N/A
Efficacy: 82.8 lumens/watt
Spacing Criteria (0/90/45): 0.97 / 0.97 / 1.1
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P202539

CATALOG NUMBER: LD6B30D010 EU6B30509730 6LBSWMH1

Luminous Intensity Polar Plot




TEST NUMBER: P202539
CATALOG NUMBER: LD6B30D010 EU6B30509730 6LBSWMH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					0	
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		0			
RCR																						
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102	100
1	111	107	104	101		108	105	102	99		101	98	96		97	95	93		94	92	90	88
2	103	96	90	85		100	94	89	84		91	86	82		87	84	81		84	81	79	77
3	95	86	79	73		92	84	78	73		81	76	71		79	74	70		76	72	69	67
4	88	77	70	64		86	76	69	63		74	67	62		71	66	62		69	65	61	59
5	81	70	62	56		79	69	61	56		67	60	55		65	59	55		63	58	54	52
6	76	64	56	50		74	63	55	50		61	54	49		59	53	49		58	53	48	47
7	70	58	50	45		69	57	50	45		56	49	44		55	48	44		53	48	44	42
8	66	54	46	40		64	53	45	40		52	45	40		50	44	40		49	44	40	38
9	62	49	42	37		61	49	42	37		48	41	37		47	41	36		46	40	36	35
10	58	46	39	34		57	45	38	34		45	38	34		44	38	33		43	37	33	32

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P202539

CATALOG NUMBER: LD6B30D010 EU6B30509730 6LBSWMH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	124.0	5.4
10°-20°	324.2	14.0
20°-30°	429.9	18.5
30°-40°	458.5	19.8
40°-50°	428.6	18.5
50°-60°	326.9	14.1
60°-70°	177.8	7.7
70°-80°	47.7	2.1
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	878.2	37.9
0°-40°	1336.7	57.7
0°-60°	2092.2	90.2
0°-90°	2318.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2318.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1341	
5°	1322	124
15°	1156	324
25°	936	430
35°	733	459
45°	558	429
55°	368	327
65°	178	178
75°	41	48
85°	0	1
90°	0	



TEST NUMBER: P202539

CATALOG NUMBER: LD6B30D010 EU6B30509730 6LBSWMH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	1340.6
2.5°	1336.3
5°	1322.1
7.5°	1292.3
10°	1258.2
12.5°	1209.9
15°	1156.0
17.5°	1102.0
20°	1043.8
22.5°	988.4
25°	935.8
27.5°	880.5
30°	827.9
32.5°	776.8
35°	732.8
37.5°	688.7
40°	643.3
42.5°	602.1
45°	558.1
47.5°	509.8
50°	464.4
52.5°	416.1
55°	367.8
57.5°	315.3
60°	267.0
62.5°	221.5
65°	177.5
67.5°	137.7
70°	100.8
72.5°	69.6
75°	41.2
77.5°	18.5
80°	4.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)