

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204797

Luminaire Tested: **LD6B30D010 EU6B30508035 6LBCSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204797
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B30D010 EU6B30508035 6LBCSMW1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH CAST MATTE WHITE TRIM
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W
DL3-29.67 W DLE-29.73 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3326.1 lumens
Efficiency: N/A
Efficacy: 118.8 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204797

CATALOG NUMBER: LD6B30D010 EU6B30508035 6LBCSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P204797

CATALOG NUMBER: LD6B30D010 EU6B30508035 6LBCSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	99	108	104	100	97	100	97	94		96	93	91		92
2	101	94	87	82	99	92	86	81	88	84	79		85	81	78		82
3	93	83	75	70	90	81	74	69	79	73	68		76	71	67		73
4	85	74	66	60	83	73	65	59	70	64	58		68	62	58		66
5	79	66	58	52	77	65	57	51	63	56	51		61	55	50		60
6	73	60	52	45	71	59	51	45	57	50	45		56	49	44		54
7	68	55	46	40	66	54	46	40	52	45	40		51	44	40		50
8	63	50	42	36	61	49	41	36	48	41	36		47	40	36		46
9	59	46	38	33	57	45	38	32	44	37	32		43	37	32		42
10	55	42	35	30	54	42	34	30	41	34	29		40	34	29		39

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204797

CATALOG NUMBER: LD6B30D010 EU6B30508035 6LBCSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	128.7	3.9
10°-20°	366.4	11.0
20°-30°	551.2	16.6
30°-40°	653.3	19.6
40°-50°	650.1	19.5
50°-60°	524.1	15.8
60°-70°	317.0	9.5
70°-80°	117.7	3.5
80°-90°	17.5	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1046.4	31.5
0°-40°	1699.6	51.1
0°-60°	2873.8	86.4
0°-90°	3326.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3326.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1358	
5°	1352	129
15°	1298	366
25°	1197	551
35°	1046	653
45°	846	650
55°	584	524
65°	318	317
75°	107	118
85°	14	18
90°	0	



TEST NUMBER: P204797

CATALOG NUMBER: LD6B30D010 EU6B30508035 6LBCSMW1

CANDELA DISTRIBUTION (FULL):

0°	
0°	1358.5
2.5°	1358.5
5°	1352.4
7.5°	1348.4
10°	1336.3
12.5°	1316.1
15°	1298.0
17.5°	1277.8
20°	1253.7
22.5°	1229.5
25°	1197.2
27.5°	1163.0
30°	1124.7
32.5°	1088.4
35°	1046.1
37.5°	1001.7
40°	949.3
42.5°	898.9
45°	846.5
47.5°	788.1
50°	723.6
52.5°	657.1
55°	584.5
57.5°	520.0
60°	447.4
62.5°	382.9
65°	318.5
67.5°	258.0
70°	201.6
72.5°	151.2
75°	106.8
77.5°	68.5
80°	40.3
82.5°	24.2
85°	14.1
87.5°	6.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)