

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205511

Luminaire Tested: **LD6B30D010 EU6B30508035 6LBMGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205511
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B30D010 EU6B30508035 6LBMGPH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH GRAPHITE HAZE TRIM
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W
DL3-29.67 W DLE-29.73 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1689.6 lumens
Efficiency: N/A
Efficacy: 60.3 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.91
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205511

CATALOG NUMBER: LD6B30D010 EU6B30508035 6LBMGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P205511

CATALOG NUMBER: LD6B30D010 EU6B30508035 6LBMGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	101		100	99	98		97
2	107	102	98	94	105	100	97	93	97	94	91		94	92	89		91
3	102	95	90	85	100	93	89	85	91	87	83		88	85	82		86
4	96	88	82	78	94	87	82	77	85	80	77		83	79	76		81
5	91	82	76	72	89	81	76	71	79	74	71		78	73	70		76
6	86	77	71	66	85	76	70	66	74	69	65		73	68	65		72
7	82	72	66	61	80	71	65	61	70	65	61		69	64	60		68
8	77	68	61	57	76	67	61	57	66	60	57		65	60	56		64
9	74	64	57	53	72	63	57	53	62	57	53		61	56	53		60
10	70	60	54	50	69	59	54	50	59	53	50		58	53	49		57

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205511

CATALOG NUMBER: LD6B30D010 EU6B30508035 6LBMGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	161.7	9.6
10°-20°	419.7	24.8
20°-30°	534.7	31.6
30°-40°	377.9	22.4
40°-50°	138.0	8.2
50°-60°	38.2	2.3
60°-70°	13.9	0.8
70°-80°	4.9	0.3
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1116.2	66.1
0°-40°	1494.1	88.4
0°-60°	1670.3	98.9
0°-90°	1689.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1689.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1761	
5°	1730	162
15°	1494	420
25°	1187	535
35°	600	378
45°	167	138
55°	41	38
65°	14	14
75°	3	5
85°	0	0
90°	0	



TEST NUMBER: P205511

CATALOG NUMBER: LD6B30D010 EU6B30508035 6LBMGPH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1760.7
2.5°	1753.8
5°	1730.0
7.5°	1682.2
10°	1631.0
12.5°	1562.8
15°	1494.5
17.5°	1426.3
20°	1358.0
22.5°	1276.1
25°	1187.4
27.5°	1064.6
30°	928.1
32.5°	764.3
35°	600.5
37.5°	457.2
40°	334.4
42.5°	242.3
45°	167.2
47.5°	112.6
50°	75.1
52.5°	51.2
55°	40.9
57.5°	30.7
60°	23.9
62.5°	17.1
65°	13.6
67.5°	10.2
70°	6.8
72.5°	6.8
75°	3.4
77.5°	3.4
80°	3.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)