

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203044

Luminaire Tested: **LD6B30D010 EU6B30508035 6LBWB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203044
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B30D010 EU6B30508035 6LBWB1
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH SPECULAR BLACK TRIM
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W
DL3-29.67 W DLE-29.73 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1703.5 lumens
Efficiency: N/A
Efficacy: 60.8 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.08 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203044

CATALOG NUMBER: LD6B30D010 EU6B30508035 6LBWB1

Luminous Intensity Polar Plot





TEST NUMBER: P203044

CATALOG NUMBER: LD6B30D010 EU6B30508035 6LBWB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			50
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			102
1	113	110	107	105	110	108	105	103		104	102	100			100	98	97			96
2	106	101	97	93	104	99	95	92		96	93	90			93	90	88			90
3	100	93	87	83	98	92	86	82		89	85	81			86	83	80			84
4	94	86	79	75	92	85	79	74		82	77	73			80	76	73			78
5	89	79	73	68	87	78	72	67		76	71	67			75	70	66			73
6	83	73	67	62	82	72	66	61		71	65	61			69	64	61			68
7	78	68	61	56	77	67	61	56		66	60	56			65	60	56			63
8	74	63	57	52	73	63	56	52		61	56	52			60	55	51			59
9	70	59	52	48	69	58	52	48		57	52	48			57	51	47			56
10	66	55	49	44	65	55	49	44		54	48	44			53	48	44			52

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203044

CATALOG NUMBER: LD6B30D010 EU6B30508035 6LBWB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	120.7	7.1
10°-20°	337.5	19.8
20°-30°	472.8	27.8
30°-40°	451.6	26.5
40°-50°	257.2	15.1
50°-60°	62.8	3.7
60°-70°	0.8	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	931.1	54.7
0°-40°	1382.7	81.2
0°-60°	1702.7	100.0
0°-90°	1703.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1703.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1284	
5°	1273	121
15°	1197	338
25°	1034	473
35°	736	452
45°	330	257
55°	62	63
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P203044

CATALOG NUMBER: LD6B30D010 EU6B30508035 6LBWB1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1283.9
2.5°	1283.9
5°	1273.4
7.5°	1259.6
10°	1249.2
12.5°	1228.3
15°	1197.1
17.5°	1169.4
20°	1134.7
22.5°	1089.5
25°	1034.0
27.5°	971.6
30°	902.2
32.5°	818.9
35°	735.6
37.5°	635.0
40°	527.4
42.5°	426.8
45°	329.6
47.5°	242.9
50°	170.0
52.5°	107.6
55°	62.5
57.5°	27.8
60°	6.9
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)