

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203688

Luminaire Tested: **LD6B50D010TE EU6B30508035 6LBNH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203688
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B50D010TE EU6B30508035 6LBNH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3448.1 lumens
Efficiency: N/A
Efficacy: 58.7 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.84
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 58.77
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203688

CATALOG NUMBER: LD6B50D010TE EU6B30508035 6LBNH1

Luminous Intensity Polar Plot





TEST NUMBER: P203688

CATALOG NUMBER: LD6B50D010TE EU6B30508035 6LBNH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	109	106	104	104	103	101		101	99	98		97
2	108	103	99	96	106	101	98	94	98	95	92		95	93	90		92
3	102	96	91	87	100	95	90	86	92	88	85		90	86	84		87
4	97	90	84	80	95	89	83	79	86	82	78		84	81	78		83
5	92	84	78	74	91	83	78	73	81	76	73		80	75	72		78
6	88	79	73	69	86	78	72	68	77	72	68		75	71	67		74
7	83	74	68	64	82	73	68	64	72	67	63		71	66	63		70
8	79	70	64	60	78	69	64	60	68	63	59		67	63	59		66
9	76	66	60	56	75	66	60	56	65	59	56		64	59	56		63
10	72	62	57	53	71	62	57	53	61	56	53		60	56	52		60

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203688

CATALOG NUMBER: LD6B50D010TE EU6B30508035 6LBNH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	397.5	11.5
10°-20°	947.9	27.5
20°-30°	1085.9	31.5
30°-40°	729.6	21.2
40°-50°	208.4	6.0
50°-60°	51.0	1.5
60°-70°	19.4	0.6
70°-80°	7.5	0.2
80°-90°	0.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2431.3	70.5
0°-40°	3161.0	91.7
0°-60°	3420.4	99.2
0°-90°	3448.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3448.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4420	
5°	4294	397
15°	3402	948
25°	2370	1086
35°	1163	730
45°	239	208
55°	57	51
65°	19	19
75°	6	7
85°	0	1
90°	0	



TEST NUMBER: P203688

CATALOG NUMBER: LD6B50D010TE EU6B30508035 6LBNH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	4420.1
2.5°	4388.7
5°	4294.4
7.5°	4124.6
10°	3917.1
12.5°	3653.1
15°	3401.6
17.5°	3137.5
20°	2873.4
22.5°	2621.9
25°	2370.4
27.5°	2137.8
30°	1867.4
32.5°	1509.0
35°	1163.2
37.5°	848.8
40°	584.7
42.5°	383.5
45°	238.9
47.5°	144.6
50°	88.0
52.5°	69.2
55°	56.6
57.5°	44.0
60°	31.4
62.5°	25.2
65°	18.9
67.5°	12.6
70°	12.6
72.5°	6.3
75°	6.3
77.5°	6.3
80°	6.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)