

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204512

Luminaire Tested: **LD6B50D010TE EU6B30508035 6LBSB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204512
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B50D010TE EU6B30508035 6LBSB1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH SPECULAR BLACK TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5018.3 lumens
Efficiency: N/A
Efficacy: 85.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.3
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 58.77
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204512

CATALOG NUMBER: LD6B50D010TE EU6B30508035 6LBSB1

Luminous Intensity Polar Plot





TEST NUMBER: P204512

CATALOG NUMBER: LD6B50D010TE EU6B30508035 6LBSB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	111	107	103	100	108	105	101	98	100	98	95		97	94	93		93
2	102	95	89	84	100	93	88	83	90	85	81		86	83	79		84
3	94	84	77	72	91	83	76	71	80	74	70		77	73	68		75
4	86	76	68	62	84	74	67	61	72	65	60		70	64	60		68
5	80	68	60	54	78	67	59	53	65	58	53		63	57	52		61
6	74	62	53	47	72	61	53	47	59	52	47		57	51	46		56
7	69	56	48	42	67	55	48	42	54	47	42		52	46	41		51
8	64	51	43	38	63	51	43	38	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		45	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		40

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204512

CATALOG NUMBER: LD6B50D010TE EU6B30508035 6LBSB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	208.9	4.2
10°-20°	592.8	11.8
20°-30°	881.9	17.6
30°-40°	1026.2	20.4
40°-50°	1000.3	19.9
50°-60°	769.3	15.3
60°-70°	425.3	8.5
70°-80°	112.6	2.2
80°-90°	0.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1683.7	33.6
0°-40°	2709.9	54.0
0°-60°	4479.5	89.3
0°-90°	5018.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5018.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2214	
5°	2201	209
15°	2099	593
25°	1915	882
35°	1648	1026
45°	1298	1000
55°	859	769
65°	426	425
75°	95	113
85°	0	1
90°	0	



TEST NUMBER: P204512

CATALOG NUMBER: LD6B50D010TE EU6B30508035 6LBSB1

CANDELA DISTRIBUTION (FULL):

0°	
0°	2213.7
2.5°	2213.7
5°	2201.0
7.5°	2181.9
10°	2169.2
12.5°	2131.0
15°	2099.2
17.5°	2067.4
20°	2022.9
22.5°	1978.4
25°	1914.8
27.5°	1851.1
30°	1787.5
32.5°	1717.6
35°	1647.6
37.5°	1558.5
40°	1482.2
42.5°	1399.5
45°	1297.7
47.5°	1202.3
50°	1094.2
52.5°	979.6
55°	858.8
57.5°	744.3
60°	636.1
62.5°	528.0
65°	426.2
67.5°	330.8
70°	241.7
72.5°	165.4
75°	95.4
77.5°	44.5
80°	6.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)