

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204183

Luminaire Tested: **LD6B30D010 EU6B30509035 6LBSH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204183
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B30D010 EU6B30509035 6LBSH1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W
DL3-29.67 W DLE-29.73 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2665.9 lumens
Efficiency: N/A
Efficacy: 95.2 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204183

CATALOG NUMBER: LD6B30D010 EU6B30509035 6LBSH1

Luminous Intensity Polar Plot






TEST NUMBER: P204183

CATALOG NUMBER: LD6B30D010 EU6B30509035 6LBSH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88		
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77		
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67		
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58		
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51		
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46		
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41		
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37		
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34		
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204183

CATALOG NUMBER: LD6B30D010 EU6B30509035 6LBSH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	130.6	4.9
10°-20°	355.0	13.3
20°-30°	493.0	18.5
30°-40°	537.9	20.2
40°-50°	501.8	18.8
50°-60°	380.9	14.3
60°-70°	208.5	7.8
70°-80°	57.4	2.2
80°-90°	0.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	978.5	36.7
0°-40°	1516.5	56.9
0°-60°	2399.1	90.0
0°-90°	2665.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2665.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1394	
5°	1382	131
15°	1265	355
25°	1071	493
35°	860	538
45°	652	502
55°	426	381
65°	208	209
75°	50	57
85°	0	1
90°	0	



TEST NUMBER: P204183

CATALOG NUMBER: LD6B30D010 EU6B30509035 6LBSH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1394.3
2.5°	1394.3
5°	1382.5
7.5°	1364.9
10°	1338.5
12.5°	1303.3
15°	1265.1
17.5°	1218.1
20°	1174.1
22.5°	1121.3
25°	1071.4
27.5°	1021.5
30°	965.7
32.5°	912.9
35°	860.0
37.5°	807.2
40°	757.3
42.5°	704.5
45°	651.6
47.5°	598.8
50°	540.1
52.5°	484.3
55°	425.6
57.5°	369.8
60°	314.1
62.5°	258.3
65°	208.4
67.5°	161.4
70°	120.3
72.5°	82.2
75°	49.9
77.5°	23.5
80°	5.9
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)