

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203050

Luminaire Tested: **LD6B30D010 EU6B30509035 6LBWB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203050
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B30D010 EU6B30509035 6LBWB1
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH SPECULAR BLACK TRIM
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W
DL3-29.67 W DLE-29.73 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1440.0 lumens
Efficiency: N/A
Efficacy: 51.4 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.08 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203050

CATALOG NUMBER: LD6B30D010 EU6B30509035 6LBWB1

Luminous Intensity Polar Plot






TEST NUMBER: P203050

CATALOG NUMBER: LD6B30D010 EU6B30509035 6LBWB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	107	105		110	108	105	103		104	102	100		100	98	97		96	95	94
2	106	101	97	93		104	99	95	92		96	93	90		93	90	88		90	88	86
3	100	93	87	83		98	92	86	82		89	85	81		86	83	80		84	81	78
4	94	86	79	75		92	85	79	74		82	77	73		80	76	73		78	75	72
5	89	79	73	68		87	78	72	67		76	71	67		75	70	66		73	69	66
6	83	73	67	62		82	72	66	61		71	65	61		69	64	61		68	64	60
7	78	68	61	56		77	67	61	56		66	60	56		65	60	56		63	59	55
8	74	63	57	52		73	63	56	52		61	56	52		60	55	51		59	55	51
9	70	59	52	48		69	58	52	48		57	52	48		57	51	47		56	51	47
10	66	55	49	44		65	55	49	44		54	48	44		53	48	44		52	47	44

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203050

CATALOG NUMBER: LD6B30D010 EU6B30509035 6LBWB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	102.0	7.1
10°-20°	285.3	19.8
20°-30°	399.7	27.8
30°-40°	381.7	26.5
40°-50°	217.4	15.1
50°-60°	53.1	3.7
60°-70°	0.7	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	787.1	54.7
0°-40°	1168.8	81.2
0°-60°	1439.3	100.0
0°-90°	1440.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1440.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1085	
5°	1076	102
15°	1012	285
25°	874	400
35°	622	382
45°	279	217
55°	53	53
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P203050

CATALOG NUMBER: LD6B30D010 EU6B30509035 6LBWB1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1085.3
2.5°	1085.3
5°	1076.5
7.5°	1064.7
10°	1055.9
12.5°	1038.3
15°	1011.9
17.5°	988.5
20°	959.1
22.5°	921.0
25°	874.1
27.5°	821.3
30°	762.6
32.5°	692.2
35°	621.8
37.5°	536.8
40°	445.8
42.5°	360.8
45°	278.7
47.5°	205.3
50°	143.7
52.5°	90.9
55°	52.8
57.5°	23.5
60°	5.9
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)