

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205308

Luminaire Tested: **LD6B30D010 EU6B30508050 6LBNLI1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P205308  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD6B30D010 EU6B30508050 6LBNLI1  
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT  
NARROW DISTRIBUTION WITH SPECULAR CLEAR TRIM  
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W  
DL3-29.67 W DLE-29.73 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2432.4 lumens  
Efficiency: N/A  
Efficacy: 86.9 lumens/watt  
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.58  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P205308

CATALOG NUMBER: LD6B30D010 EU6B30508050 6LBNLI1

### Luminous Intensity Polar Plot






TEST NUMBER: P205308

CATALOG NUMBER: LD6B30D010 EU6B30508050 6LBNLI1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |  |     |     |     |     |  |     |     |     |  |     |     |     |  |     |     |     |
|-----|-----|-----|-----|-----|--|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|
| RF  | 20  |     |     |     |  | 20  |     |     |     |  | 20  |     |     |  |     | 20  |     |  |     |     | 20  |
| RC  | 80  |     |     |     |  | 70  |     |     |     |  | 50  |     |     |  |     | 30  |     |  |     |     | 10  |
| RW  | 70  | 50  | 30  | 10  |  | 70  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  |
| RCR |     |     |     |     |  |     |     |     |     |  |     |     |     |  |     |     |     |  |     |     |     |
| 0   | 119 | 119 | 119 | 119 |  | 116 | 116 | 116 | 116 |  | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 | 102 | 102 |
| 1   | 114 | 112 | 109 | 107 |  | 112 | 109 | 107 | 106 |  | 105 | 104 | 102 |  | 102 | 101 | 99  |  | 98  | 97  | 96  |
| 2   | 109 | 105 | 101 | 98  |  | 107 | 103 | 100 | 97  |  | 100 | 97  | 95  |  | 97  | 95  | 93  |  | 94  | 93  | 91  |
| 3   | 105 | 99  | 94  | 91  |  | 103 | 97  | 93  | 90  |  | 95  | 91  | 89  |  | 93  | 90  | 87  |  | 90  | 88  | 86  |
| 4   | 100 | 93  | 88  | 85  |  | 98  | 92  | 88  | 84  |  | 90  | 86  | 83  |  | 88  | 85  | 82  |  | 86  | 84  | 81  |
| 5   | 96  | 88  | 83  | 79  |  | 94  | 87  | 83  | 79  |  | 86  | 82  | 78  |  | 84  | 81  | 78  |  | 83  | 80  | 77  |
| 6   | 92  | 84  | 79  | 75  |  | 90  | 83  | 78  | 75  |  | 82  | 77  | 74  |  | 80  | 76  | 74  |  | 79  | 76  | 73  |
| 7   | 88  | 80  | 74  | 71  |  | 87  | 79  | 74  | 71  |  | 78  | 73  | 70  |  | 77  | 73  | 70  |  | 76  | 72  | 69  |
| 8   | 84  | 76  | 71  | 67  |  | 83  | 75  | 70  | 67  |  | 74  | 70  | 67  |  | 73  | 69  | 66  |  | 73  | 69  | 66  |
| 9   | 81  | 73  | 67  | 64  |  | 80  | 72  | 67  | 64  |  | 71  | 67  | 63  |  | 70  | 66  | 63  |  | 70  | 66  | 63  |
| 10  | 78  | 69  | 64  | 61  |  | 77  | 69  | 64  | 61  |  | 68  | 64  | 61  |  | 67  | 63  | 60  |  | 67  | 63  | 60  |

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P205308

CATALOG NUMBER: LD6B30D010 EU6B30508050 6LBNLI1

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 460.5  | 18.9      |
| 10°-20°   | 826.5  | 34.0      |
| 20°-30°   | 668.2  | 27.5      |
| 30°-40°   | 384.9  | 15.8      |
| 40°-50°   | 81.4   | 3.3       |
| 50°-60°   | 7.0    | 0.3       |
| 60°-70°   | 3.5    | 0.1       |
| 70°-80°   | 0.5    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 1955.1 | 80.4      |
| 0°-40°    | 2340.1 | 96.2      |
| 0°-60°    | 2428.5 | 99.8      |
| 0°-90°    | 2432.4 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 2432.4 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 5538 |      |
| 5°  | 5159 | 460  |
| 15° | 3002 | 826  |
| 25° | 1442 | 668  |
| 35° | 610  | 385  |
| 45° | 88   | 81   |
| 55° | 7    | 7    |
| 65° | 4    | 3    |
| 75° | 0    | 0    |
| 85° | 0    | 0    |
| 90° | 0    |      |



TEST NUMBER: P205308

CATALOG NUMBER: LD6B30D010 EU6B30508050 6LBNLI1

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     |
|-------|--------|
| 0°    | 5538.1 |
| 2.5°  | 5471.5 |
| 5°    | 5159.4 |
| 7.5°  | 4710.4 |
| 10°   | 4159.7 |
| 12.5° | 3595.1 |
| 15°   | 3002.3 |
| 17.5° | 2430.6 |
| 20°   | 2013.2 |
| 22.5° | 1694.1 |
| 25°   | 1441.5 |
| 27.5° | 1227.6 |
| 30°   | 1034.7 |
| 32.5° | 820.7  |
| 35°   | 610.3  |
| 37.5° | 424.4  |
| 40°   | 277.1  |
| 42.5° | 168.4  |
| 45°   | 87.7   |
| 47.5° | 35.1   |
| 50°   | 10.5   |
| 52.5° | 10.5   |
| 55°   | 7.0    |
| 57.5° | 7.0    |
| 60°   | 3.5    |
| 62.5° | 3.5    |
| 65°   | 3.5    |
| 67.5° | 3.5    |
| 70°   | 3.5    |
| 72.5° | 0.0    |
| 75°   | 0.0    |
| 77.5° | 0.0    |
| 80°   | 0.0    |
| 82.5° | 0.0    |
| 85°   | 0.0    |
| 87.5° | 0.0    |
| 90°   | 0.0    |



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)