

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204927

Luminaire Tested: **LD6B50D010TE EU6B30508040 6LBCSMB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204927
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B50D010TE EU6B30508040 6LBCSMB1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH CAST MATTE BLACK TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5138.2 lumens
Efficiency: N/A
Efficacy: 87.4 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 58.77
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204927

CATALOG NUMBER: LD6B50D010TE EU6B30508040 6LBSCMB1

Luminous Intensity Polar Plot





TEST NUMBER: P204927

CATALOG NUMBER: LD6B50D010TE EU6B30508040 6LBCSMB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	111	107	103	100		108	104	101	98		100	98	95		96	94	92		93	91	90
2	102	95	89	84		99	93	87	83		89	85	81		86	82	79		83	80	77
3	93	84	77	71		91	83	76	70		80	74	69		77	72	68		74	70	67
4	86	75	67	61		84	74	66	61		71	65	60		69	63	59		67	62	58
5	79	67	59	53		77	66	59	53		64	57	52		62	56	52		61	55	51
6	74	61	53	47		72	60	52	46		58	51	46		57	50	46		55	50	45
7	68	55	47	41		67	55	47	41		53	46	41		52	45	41		50	45	40
8	64	51	43	37		62	50	42	37		49	42	37		48	41	37		46	41	36
9	60	47	39	33		58	46	39	33		45	38	33		44	38	33		43	37	33
10	56	43	35	30		55	43	35	30		42	35	30		41	34	30		40	34	30

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204927

CATALOG NUMBER: LD6B50D010TE EU6B30508040 6LBCSMB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	205.2	4.0
10°-20°	584.6	11.4
20°-30°	878.9	17.1
30°-40°	1042.8	20.3
40°-50°	1032.0	20.1
50°-60°	810.6	15.8
60°-70°	454.5	8.8
70°-80°	127.6	2.5
80°-90°	2.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1668.7	32.5
0°-40°	2711.6	52.8
0°-60°	4554.1	88.6
0°-90°	5138.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5138.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2170	
5°	2166	205
15°	2074	585
25°	1908	879
35°	1672	1043
45°	1344	1032
55°	914	811
65°	453	454
75°	110	128
85°	0	2
90°	0	



TEST NUMBER: P204927

CATALOG NUMBER: LD6B50D010TE EU6B30508040 6LBCSMB1

CANDELA DISTRIBUTION (FULL):

0°	
0°	2169.6
2.5°	2162.3
5°	2166.0
7.5°	2147.5
10°	2125.4
12.5°	2099.7
15°	2073.9
17.5°	2040.7
20°	1996.5
22.5°	1952.3
25°	1908.1
27.5°	1860.2
30°	1797.6
32.5°	1735.0
35°	1672.4
37.5°	1598.7
40°	1514.0
42.5°	1432.9
45°	1344.5
47.5°	1245.1
50°	1141.9
52.5°	1024.0
55°	913.5
57.5°	788.3
60°	670.4
62.5°	563.6
65°	453.1
67.5°	357.3
70°	265.2
72.5°	180.5
75°	110.5
77.5°	55.3
80°	14.7
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)