

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203901

Luminaire Tested: **LD6B50D010TE EU6B30509040 6LBNGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203901
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B50D010TE EU6B30509040 6LBNGPH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH GRAPHITE HAZE TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2332.7 lumens
Efficiency: N/A
Efficacy: 39.7 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.88
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 58.77
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203901

CATALOG NUMBER: LD6B50D010TE EU6B30509040 6LBNGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P203901

CATALOG NUMBER: LD6B50D010TE EU6B30509040 6LBNGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			0
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			100
1	114	111	108	106		111	109	106	104		105	103	101			101	100	98			94
2	108	103	99	96		106	101	98	95		98	95	93			95	93	91			87
3	103	96	91	87		101	95	90	87		92	88	85			90	87	84			81
4	97	90	84	80		96	89	84	80		87	82	79			85	81	78			76
5	93	84	78	74		91	83	78	74		82	77	73			80	76	73			70
6	88	79	73	69		86	78	73	69		77	72	68			75	71	68			66
7	84	74	68	64		82	74	68	64		72	67	64			71	67	63			62
8	79	70	64	60		78	69	64	60		68	63	60			67	63	59			58
9	76	66	60	56		75	66	60	56		65	60	56			64	59	56			54
10	72	63	57	53		71	62	57	53		61	56	53			61	56	53			51

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203901

CATALOG NUMBER: LD6B50D010TE EU6B30509040 6LBNGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	256.7	11.0
10°-20°	633.1	27.1
20°-30°	767.0	32.9
30°-40°	522.7	22.4
40°-50°	124.5	5.3
50°-60°	19.5	0.8
60°-70°	7.2	0.3
70°-80°	2.1	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1656.7	71.0
0°-40°	2179.5	93.4
0°-60°	2323.4	99.6
0°-90°	2332.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2332.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2836	
5°	2756	257
15°	2266	633
25°	1676	767
35°	835	523
45°	133	124
55°	21	19
65°	5	7
75°	0	2
85°	0	0
90°	0	



TEST NUMBER: P203901

CATALOG NUMBER: LD6B50D010TE EU6B30509040 6LBNGPH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2835.5
2.5°	2819.5
5°	2755.7
7.5°	2670.5
10°	2548.2
12.5°	2409.9
15°	2266.2
17.5°	2117.3
20°	1968.3
22.5°	1819.4
25°	1675.7
27.5°	1542.7
30°	1351.2
32.5°	1101.2
35°	835.2
37.5°	595.8
40°	393.7
42.5°	244.7
45°	133.0
47.5°	69.2
50°	37.2
52.5°	26.6
55°	21.3
57.5°	16.0
60°	10.6
62.5°	10.6
65°	5.3
67.5°	5.3
70°	5.3
72.5°	5.3
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)