

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203464

Luminaire Tested: **LD6B30D010 EU6B30509050 6LBMB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203464
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B30D010 EU6B30509050 6LBMB1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH SPECULAR BLACK TRIM
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W
DL3-29.67 W DLE-29.73 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1121.2 lumens
Efficiency: N/A
Efficacy: 40.0 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.86
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203464

CATALOG NUMBER: LD6B30D010 EU6B30509050 6LBMB1

Luminous Intensity Polar Plot





TEST NUMBER: P203464

CATALOG NUMBER: LD6B30D010 EU6B30509050 6LBMB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			50
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			102
1	114	111	109	106	111	109	107	105		105	103	102			101	100	99			98
2	108	104	100	96	106	102	98	95		99	96	93			96	93	91			93
3	103	97	92	88	101	95	91	87		93	89	86			90	87	85			88
4	98	91	85	81	96	90	85	81		87	83	80			85	82	79			84
5	93	85	79	75	92	84	79	75		82	78	74			81	77	74			79
6	89	80	74	70	87	79	74	70		78	73	69			76	72	69			75
7	84	75	69	65	83	75	69	65		73	68	65			72	68	65			71
8	80	71	65	61	79	71	65	61		69	64	61			68	64	61			67
9	77	67	61	58	76	67	61	57		66	61	57			65	60	57			64
10	73	64	58	54	72	63	58	54		62	57	54			62	57	54			61

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203464

CATALOG NUMBER: LD6B30D010 EU6B30509050 6LBMB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	128.0	11.4
10°-20°	316.0	28.2
20°-30°	380.6	33.9
30°-40°	240.8	21.5
40°-50°	55.1	4.9
50°-60°	0.6	0.1
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	824.7	73.6
0°-40°	1065.5	95.0
0°-60°	1121.2	100.0
0°-90°	1121.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1121.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1412	
5°	1380	128
15°	1128	316
25°	843	381
35°	380	241
45°	61	55
55°	0	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P203464

CATALOG NUMBER: LD6B30D010 EU6B30509050 6LBMB1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1411.5
2.5°	1405.7
5°	1379.6
7.5°	1330.4
10°	1269.5
12.5°	1197.0
15°	1127.5
17.5°	1060.8
20°	991.2
22.5°	921.7
25°	843.4
27.5°	750.7
30°	637.6
32.5°	510.1
35°	379.7
37.5°	269.5
40°	182.6
42.5°	113.0
45°	60.9
47.5°	26.1
50°	5.8
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)