

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204391

Luminaire Tested: **LD6B30D010 EU6B30509050 6LBSGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204391
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B30D010 EU6B30509050 6LBSGPH1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH GRAPHITE HAZE TRIM
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W
DL3-29.67 W DLE-29.73 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2460.8 lumens
Efficiency: N/A
Efficacy: 87.9 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.26
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204391

CATALOG NUMBER: LD6B30D010 EU6B30509050 6LBSGPH1

Luminous Intensity Polar Plot






TEST NUMBER: P204391

CATALOG NUMBER: LD6B30D010 EU6B30509050 6LBSGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	111	107	103	100		108	105	102	99		101	98	96		97	95	93		93	91	90
2	102	95	89	84		100	93	88	83		90	85	82		87	83	80		84	81	78
3	94	85	78	72		92	83	77	71		80	75	70		78	73	69		75	71	68
4	87	76	68	62		85	75	67	62		72	66	61		70	65	60		68	63	59
5	80	68	60	54		78	67	60	54		65	59	53		63	58	53		62	56	52
6	74	62	54	48		73	61	53	48		59	52	47		58	52	47		56	51	47
7	69	57	48	43		68	56	48	43		54	47	42		53	47	42		52	46	42
8	65	52	44	38		63	51	44	38		50	43	38		49	42	38		48	42	38
9	60	48	40	35		59	47	40	35		46	39	35		45	39	34		44	38	34
10	57	44	37	32		56	44	36	32		43	36	31		42	36	31		41	35	31

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204391

CATALOG NUMBER: LD6B30D010 EU6B30509050 6LBSGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	107.6	4.4
10°-20°	302.1	12.3
20°-30°	440.5	17.9
30°-40°	502.4	20.4
40°-50°	481.9	19.6
50°-60°	369.1	15.0
60°-70°	202.5	8.2
70°-80°	53.9	2.2
80°-90°	0.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	850.2	34.5
0°-40°	1352.6	55.0
0°-60°	2203.6	89.5
0°-90°	2460.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2460.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1143	
5°	1134	108
15°	1072	302
25°	957	441
35°	803	502
45°	626	482
55°	413	369
65°	204	203
75°	47	54
85°	0	1
90°	0	



TEST NUMBER: P204391

CATALOG NUMBER: LD6B30D010 EU6B30509050 6LBSGPH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	1142.9
2.5°	1139.9
5°	1134.0
7.5°	1125.2
10°	1113.4
12.5°	1092.7
15°	1072.0
17.5°	1048.4
20°	1021.8
22.5°	989.3
25°	956.8
27.5°	924.4
30°	883.0
32.5°	844.6
35°	803.3
37.5°	761.9
40°	720.6
42.5°	676.3
45°	626.1
47.5°	575.9
50°	522.7
52.5°	466.6
55°	413.4
57.5°	360.3
60°	304.2
62.5°	251.0
65°	203.8
67.5°	156.5
70°	115.2
72.5°	76.8
75°	47.3
77.5°	20.7
80°	5.9
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)