

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P202666

Luminaire Tested: **LD6B50D010TE EU6B30509050 6LBMWMH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P202666
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B50D010TE EU6B30509050 6LBMWMH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH WARM HAZE TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3654.5 lumens
Efficiency: N/A
Efficacy: 62.2 lumens/watt
Spacing Criteria (0/90/45): 0.9 / 0.9 / 0.89
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 58.77
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P202666

CATALOG NUMBER: LD6B50D010TE EU6B30509050 6LBMWMH1

Luminous Intensity Polar Plot






TEST NUMBER: P202666

CATALOG NUMBER: LD6B50D010TE EU6B30509050 6LBMWMH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	111	108	106		111	108	106	104		104	103	101		101	99	98		97	96	95
2	108	103	99	95		105	101	97	94		98	95	92		95	92	90		92	90	88
3	102	95	90	86		100	94	89	86		91	88	84		89	86	83		87	84	82
4	97	89	83	79		95	88	83	79		86	81	78		84	80	77		82	79	76
5	92	83	77	73		90	82	77	73		80	76	72		79	75	71		77	74	71
6	87	78	72	67		85	77	71	67		76	71	67		74	70	66		73	69	66
7	83	73	67	63		81	72	67	63		71	66	62		70	65	62		69	65	61
8	78	69	63	58		77	68	62	58		67	62	58		66	61	58		65	61	58
9	75	65	59	55		73	64	59	55		63	58	54		62	58	54		62	57	54
10	71	61	55	51		70	61	55	51		60	55	51		59	54	51		58	54	51

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P202666

CATALOG NUMBER: LD6B50D010TE EU6B30509050 6LBMWMH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	373.0	10.2
10°-20°	957.5	26.2
20°-30°	1176.1	32.2
30°-40°	806.4	22.1
40°-50°	259.2	7.1
50°-60°	52.5	1.4
60°-70°	20.7	0.6
70°-80°	7.8	0.2
80°-90°	1.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2506.6	68.6
0°-40°	3313.0	90.7
0°-60°	3624.8	99.2
0°-90°	3654.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3654.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4064	
5°	3986	373
15°	3425	958
25°	2595	1176
35°	1286	806
45°	307	259
55°	53	53
65°	22	21
75°	6	8
85°	0	1
90°	0	



TEST NUMBER: P202666

CATALOG NUMBER: LD6B50D010TE EU6B30509050 6LBMWMH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	4064.0
2.5°	4039.2
5°	3986.5
7.5°	3887.3
10°	3754.0
12.5°	3589.7
15°	3425.4
17.5°	3242.5
20°	3041.0
22.5°	2830.2
25°	2594.6
27.5°	2334.2
30°	2005.7
32.5°	1643.0
35°	1286.5
37.5°	961.0
40°	691.3
42.5°	471.2
45°	306.9
47.5°	189.1
50°	114.7
52.5°	71.3
55°	52.7
57.5°	40.3
60°	31.0
62.5°	24.8
65°	21.7
67.5°	15.5
70°	12.4
72.5°	9.3
75°	6.2
77.5°	6.2
80°	3.1
82.5°	3.1
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)