

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P202846

Luminaire Tested: **LD6B30D010 EU6B30509050 6LBWWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P202846
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B30D010 EU6B30509050 6LBWWH1
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W
DL3-29.67 W DLE-29.73 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2354.6 lumens
Efficiency: N/A
Efficacy: 84.1 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.18
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P202846

CATALOG NUMBER: LD6B30D010 EU6B30509050 6LBWWH1

Luminous Intensity Polar Plot





TEST NUMBER: P202846

CATALOG NUMBER: LD6B30D010 EU6B30509050 6LBWWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	109	107	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	98	94	91	95	92	89		92	89	87		89
3	99	92	86	81	97	90	85	81	88	83	79		85	81	78		83
4	93	84	78	73	91	83	77	72	81	76	71		79	74	71		77
5	87	77	71	66	85	76	70	65	75	69	65		73	68	64		71
6	82	71	64	59	80	71	64	59	69	63	59		67	62	58		66
7	77	66	59	54	75	65	59	54	64	58	54		63	57	53		61
8	72	61	54	49	71	61	54	49	59	53	49		58	53	49		57
9	68	57	50	45	67	56	50	45	55	49	45		54	49	45		53
10	64	53	46	42	63	53	46	42	52	46	42		51	45	42		50

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P202846

CATALOG NUMBER: LD6B30D010 EU6B30509050 6LBWWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	140.6	6.0
10°-20°	418.0	17.8
20°-30°	629.2	26.7
30°-40°	643.4	27.3
40°-50°	390.7	16.6
50°-60°	110.0	4.7
60°-70°	16.7	0.7
70°-80°	5.5	0.2
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1187.8	50.4
0°-40°	1831.2	77.8
0°-60°	2331.9	99.0
0°-90°	2354.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2354.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1462	
5°	1468	141
15°	1480	418
25°	1374	629
35°	1043	643
45°	502	391
55°	109	110
65°	15	17
75°	6	5
85°	0	0
90°	0	



TEST NUMBER: P202846

CATALOG NUMBER: LD6B30D010 EU6B30509050 6LBWWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1462.4
2.5°	1462.4
5°	1468.3
7.5°	1477.2
10°	1477.2
12.5°	1483.1
15°	1480.1
17.5°	1474.2
20°	1453.6
22.5°	1424.0
25°	1373.8
27.5°	1317.7
30°	1240.8
32.5°	1149.3
35°	1042.9
37.5°	924.7
40°	788.8
42.5°	647.0
45°	502.2
47.5°	372.3
50°	262.9
52.5°	177.3
55°	109.3
57.5°	65.0
60°	32.5
62.5°	20.7
65°	14.8
67.5°	11.8
70°	8.9
72.5°	5.9
75°	5.9
77.5°	3.0
80°	3.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)