

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204811

Luminaire Tested: **LD6B40D010 EU6B30508040 6LBCSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204811
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B40D010 EU6B30508040 6LBSCMW1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH CAST MATTE WHITE TRIM
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57
W DL3-44.71 W DLE-39.33 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4753.0 lumens
Efficiency: N/A
Efficacy: 113.7 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204811

CATALOG NUMBER: LD6B40D010 EU6B30508040 6LBCSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P204811

CATALOG NUMBER: LD6B40D010 EU6B30508040 6LBCSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	99	108	104	100	97	100	97	94		96	93	91		92
2	101	94	87	82	99	92	86	81	88	84	79		85	81	78		82
3	93	83	75	70	90	81	74	69	79	73	68		76	71	67		73
4	85	74	66	60	83	73	65	59	70	64	58		68	62	58		66
5	79	66	58	52	77	65	57	51	63	56	51		61	55	50		60
6	73	60	52	45	71	59	51	45	57	50	45		56	49	44		54
7	68	55	46	40	66	54	46	40	52	45	40		51	44	40		50
8	63	50	42	36	61	49	41	36	48	41	36		47	40	36		46
9	59	46	38	33	57	45	38	32	44	37	32		43	37	32		42
10	55	42	35	30	54	42	34	30	41	34	29		40	34	29		39

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204811

CATALOG NUMBER: LD6B40D010 EU6B30508040 6LBCSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	183.9	3.9
10°-20°	523.6	11.0
20°-30°	787.7	16.6
30°-40°	933.5	19.6
40°-50°	929.0	19.5
50°-60°	748.9	15.8
60°-70°	453.1	9.5
70°-80°	168.2	3.5
80°-90°	25.1	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1495.3	31.5
0°-40°	2428.8	51.1
0°-60°	4106.7	86.4
0°-90°	4753.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4753.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1941	
5°	1933	184
15°	1855	524
25°	1711	788
35°	1495	934
45°	1210	929
55°	835	749
65°	455	453
75°	153	168
85°	20	25
90°	0	



TEST NUMBER: P204811

CATALOG NUMBER: LD6B40D010 EU6B30508040 6LBCSMW1

CANDELA DISTRIBUTION (FULL):

0°	
0°	1941.3
2.5°	1941.3
5°	1932.6
7.5°	1926.9
10°	1909.6
12.5°	1880.8
15°	1854.9
17.5°	1826.1
20°	1791.5
22.5°	1756.9
25°	1710.9
27.5°	1661.9
30°	1607.2
32.5°	1555.3
35°	1494.8
37.5°	1431.5
40°	1356.6
42.5°	1284.6
45°	1209.7
47.5°	1126.2
50°	1034.0
52.5°	939.0
55°	835.3
57.5°	743.1
60°	639.4
62.5°	547.2
65°	455.1
67.5°	368.7
70°	288.0
72.5°	216.0
75°	152.7
77.5°	97.9
80°	57.6
82.5°	34.6
85°	20.2
87.5°	8.6
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)