

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P563913

Luminaire Tested: **LX6C20D010 EX6C209030 6LBMDH**

Issue Date: 2/15/2022

Test Information

Test Method: LM-79-08
Report Number: P563913
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-21)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C20D010 EX6C209030 6LBMDH
Description: 6 INCH 2000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 6LRMD45 TRIM WITH H FINISH, DIM TO WARM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1498.3 lumens
Efficiency: N/A
Efficacy: 68.7 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.8
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 21.8
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P563913

CATALOG NUMBER: LX6C20D010 EX6C209030 6LBMDH

Luminous Intensity Polar Plot





TEST NUMBER: P563913

CATALOG NUMBER: LX6C20D010 EX6C209030 6LBMDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	80	86	82	79	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70			
6	88	79	73	69	86	78	73	69	77	72	68	75	71	68	74	70	67	66			
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62			
8	80	70	64	60	78	70	64	60	68	63	60	67	63	59	66	62	59	58			
9	76	66	60	56	75	66	60	56	65	60	56	64	59	56	63	59	56	54			
10	72	63	57	53	71	62	57	53	62	56	53	61	56	53	60	56	53	51			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	107957
5°	104617
10°	96335
15°	86402
20°	76884
25°	63844
30°	45615
35°	29319
40°	17862
45°	9931
50°	4401
55°	2552
60°	1677
65°	1193
70°	850
75°	657
80°	410
85°	252



TEST NUMBER: P563913

CATALOG NUMBER: LX6C20D010 EX6C209030 6LBMDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	176.0	11.7
10°-20°	425.9	28.4
20°-30°	473.7	31.6
30°-40°	280.7	18.7
40°-50°	102.8	6.9
50°-60°	25.8	1.7
60°-70°	9.4	0.6
70°-80°	3.3	0.2
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1075.6	71.8
0°-40°	1356.3	90.5
0°-60°	1485.0	99.1
0°-90°	1498.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1498.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1969	
5°	1901	176
15°	1522	426
25°	1056	474
35°	438	281
45°	128	103
55°	27	26
65°	9	9
75°	3	3
85°	0	1
90°	0	



TEST NUMBER: P563913

CATALOG NUMBER: LX6C20D010 EX6C209030 6LBMDH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1969.3
2.5°	1951.9
5°	1901.1
7.5°	1824.1
10°	1730.6
12.5°	1627.4
15°	1522.4
17.5°	1420.6
20°	1317.9
22.5°	1198.5
25°	1055.5
27.5°	891.1
30°	720.6
32.5°	568.0
35°	438.1
37.5°	332.7
40°	249.6
42.5°	181.9
45°	128.1
47.5°	81.4
50°	51.6
52.5°	36.3
55°	26.7
57.5°	20.1
60°	15.3
62.5°	11.8
65°	9.2
67.5°	7.0
70°	5.3
72.5°	4.0
75°	3.1
77.5°	2.1
80°	1.3
82.5°	0.9
85°	0.4
87.5°	0.4
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)