

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P685033

Luminaire Tested: **LX6C45D010 EX6459050 6LBNLI**

Issue Date: 2/14/2022



Test Information

Test Method: LM-79-08
Report Number: P685033
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205310)
Test Lab: INNOVATION CENTER
Issue Date: 2/14/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C45D010 EX6459050 6LBNLI
Description: 6 INCH 4500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, 90CRI LEDS
AND 6LBN TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3924.0 lumens
Efficiency: N/A
Efficacy: 79.1 lumens/watt
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.58
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 49.6
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P685033

CATALOG NUMBER: LX6C45D010 EX6459050 6LBNLI

Luminous Intensity Polar Plot





TEST NUMBER: P685033

CATALOG NUMBER: LX6C45D010 EX6459050 6LBNLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	112	109	107	112	109	107	106	105	104	102	102	101	99	98	97	96	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	89
3	105	99	94	91	103	97	93	90	95	91	89	93	90	87	90	88	86	85
4	100	93	88	85	98	92	88	84	90	86	83	88	85	82	86	84	81	80
5	96	88	83	79	94	87	83	79	86	82	78	84	81	78	83	80	77	76
6	92	84	79	75	90	83	78	75	82	77	74	80	76	74	79	76	73	72
7	88	80	74	71	87	79	74	71	78	73	70	77	73	70	76	72	69	68
8	84	76	71	67	83	75	70	67	74	70	67	73	69	66	73	69	66	65
9	81	73	67	64	80	72	67	64	71	67	63	70	66	63	70	66	63	62
10	78	69	64	61	77	69	64	61	68	64	61	67	63	60	67	63	60	59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	489763
5°	458011
10°	373546
15°	274882
20°	189466
25°	140657
30°	105655
35°	65886
40°	31981
45°	10970
50°	1441
55°	1090
60°	625
65°	739
70°	914
75°	0
80°	0
85°	0



TEST NUMBER: P685033

CATALOG NUMBER: LX6C45D010 EX6459050 6LBNLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	742.8	18.9
10°-20°	1333.3	34.0
20°-30°	1078.0	27.5
30°-40°	621.0	15.8
40°-50°	131.3	3.3
50°-60°	11.3	0.3
60°-70°	5.7	0.1
70°-80°	0.7	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3154.0	80.4
0°-40°	3775.0	96.2
0°-60°	3917.6	99.8
0°-90°	3924.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3924.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8934	
5°	8323	743
15°	4843	1333
25°	2325	1078
35°	984	621
45°	142	131
55°	11	11
65°	6	6
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P685033

CATALOG NUMBER: LX6C45D010 EX6459050 6LBNLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	8934.0
2.5°	8826.7
5°	8323.0
7.5°	7598.8
10°	6710.5
12.5°	5799.6
15°	4843.4
17.5°	3921.1
20°	3247.7
22.5°	2732.9
25°	2325.4
27.5°	1980.4
30°	1669.1
32.5°	1324.0
35°	984.5
37.5°	684.6
40°	446.9
42.5°	271.6
45°	141.5
47.5°	56.5
50°	16.9
52.5°	16.9
55°	11.4
57.5°	11.4
60°	5.7
62.5°	5.7
65°	5.7
67.5°	5.7
70°	5.7
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)