

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203882

Luminaire Tested: **LD6B40D010 EU6B30508040 6LBNGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203882
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B40D010 EU6B30508040 6LBNGPH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH GRAPHITE HAZE TRIM
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57
W DL3-44.71 W DLE-39.33 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2176.5 lumens
Efficiency: N/A
Efficacy: 52.1 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.88
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203882

CATALOG NUMBER: LD6B40D010 EU6B30508040 6LBNGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P203882

CATALOG NUMBER: LD6B40D010 EU6B30508040 6LBNGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	100	98		97
2	108	103	99	96	106	101	98	95	98	95	93		95	93	91		92
3	103	96	91	87	101	95	90	87	92	88	85		90	87	84		88
4	97	90	84	80	96	89	84	80	87	82	79		85	81	78		83
5	93	84	78	74	91	83	78	74	82	77	73		80	76	73		78
6	88	79	73	69	86	78	73	69	77	72	68		75	71	68		74
7	84	74	68	64	82	74	68	64	72	67	64		71	67	63		70
8	79	70	64	60	78	69	64	60	68	63	60		67	63	59		66
9	76	66	60	56	75	66	60	56	65	60	56		64	59	56		63
10	72	63	57	53	71	62	57	53	61	56	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203882

CATALOG NUMBER: LD6B40D010 EU6B30508040 6LBNGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	239.5	11.0
10°-20°	590.7	27.1
20°-30°	715.6	32.9
30°-40°	487.7	22.4
40°-50°	116.1	5.3
50°-60°	18.2	0.8
60°-70°	6.7	0.3
70°-80°	2.0	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1545.8	71.0
0°-40°	2033.5	93.4
0°-60°	2167.8	99.6
0°-90°	2176.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2176.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2646	
5°	2571	239
15°	2114	591
25°	1564	716
35°	779	488
45°	124	116
55°	20	18
65°	5	7
75°	0	2
85°	0	0
90°	0	



TEST NUMBER: P203882

CATALOG NUMBER: LD6B40D010 EU6B30508040 6LBNGPH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2645.6
2.5°	2630.7
5°	2571.1
7.5°	2491.7
10°	2377.6
12.5°	2248.5
15°	2114.5
17.5°	1975.5
20°	1836.5
22.5°	1697.5
25°	1563.5
27.5°	1439.4
30°	1260.7
32.5°	1027.5
35°	779.3
37.5°	555.9
40°	367.3
42.5°	228.3
45°	124.1
47.5°	64.5
50°	34.7
52.5°	24.8
55°	19.9
57.5°	14.9
60°	9.9
62.5°	9.9
65°	5.0
67.5°	5.0
70°	5.0
72.5°	5.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)