

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205319

Luminaire Tested: **LD6B40D010 EU6B30508040 6LBNLI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205319
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B40D010 EU6B30508040 6LBNLI1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH SPECULAR CLEAR TRIM
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57
W DL3-44.71 W DLE-39.33 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3440.8 lumens
Efficiency: N/A
Efficacy: 82.3 lumens/watt
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.58
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205319

CATALOG NUMBER: LD6B40D010 EU6B30508040 6LBNLI1

Luminous Intensity Polar Plot





TEST NUMBER: P205319

CATALOG NUMBER: LD6B40D010 EU6B30508040 6LBNLI1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			50
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			102
1	114	112	109	107	112	109	107	106		105	104	102			102	101	99			98
2	109	105	101	98	107	103	100	97		100	97	95			97	95	93			94
3	105	99	94	91	103	97	93	90		95	91	89			93	90	87			90
4	100	93	88	85	98	92	88	84		90	86	83			88	85	82			86
5	96	88	83	79	94	87	83	79		86	82	78			84	81	78			83
6	92	84	79	75	90	83	78	75		82	77	74			80	76	74			79
7	88	80	74	71	87	79	74	71		78	73	70			77	73	70			76
8	84	76	71	67	83	75	70	67		74	70	67			73	69	66			73
9	81	73	67	64	80	72	67	64		71	67	63			70	66	63			70
10	78	69	64	61	77	69	64	61		68	64	61			67	63	60			67

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205319

CATALOG NUMBER: LD6B40D010 EU6B30508040 6LBNLI1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	651.3	18.9
10°-20°	1169.1	34.0
20°-30°	945.2	27.5
30°-40°	544.5	15.8
40°-50°	115.1	3.3
50°-60°	9.9	0.3
60°-70°	5.0	0.1
70°-80°	0.6	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2765.6	80.4
0°-40°	3310.2	96.2
0°-60°	3435.2	99.8
0°-90°	3440.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3440.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7834	
5°	7298	651
15°	4247	1169
25°	2039	945
35°	863	545
45°	124	115
55°	10	10
65°	5	5
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P205319

CATALOG NUMBER: LD6B40D010 EU6B30508040 6LBNLI1

CANDELA DISTRIBUTION (FULL):

	0°
0°	7833.9
2.5°	7739.7
5°	7298.1
7.5°	6663.1
10°	5884.1
12.5°	5085.4
15°	4246.9
17.5°	3438.2
20°	2847.8
22.5°	2396.3
25°	2039.1
27.5°	1736.5
30°	1463.6
32.5°	1160.9
35°	863.3
37.5°	600.3
40°	391.9
42.5°	238.1
45°	124.0
47.5°	49.6
50°	14.9
52.5°	14.9
55°	9.9
57.5°	9.9
60°	5.0
62.5°	5.0
65°	5.0
67.5°	5.0
70°	5.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)