

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204500

Luminaire Tested: **LD6B40D010 EU6B30508040 6LBSB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204500
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B40D010 EU6B30508040 6LBSB1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH SPECULAR BLACK TRIM
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57
W DL3-44.71 W DLE-39.33 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3961.4 lumens
Efficiency: N/A
Efficacy: 94.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.3
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204500

CATALOG NUMBER: LD6B40D010 EU6B30508040 6LBSB1

Luminous Intensity Polar Plot





TEST NUMBER: P204500

CATALOG NUMBER: LD6B40D010 EU6B30508040 6LBSB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	107	103	100	108	105	101	98	100	98	95	97	94	93	93	91	90	88		
2	102	95	89	84	100	93	88	83	90	85	81	86	83	79	84	80	78	76		
3	94	84	77	72	91	83	76	71	80	74	70	77	73	68	75	71	67	65		
4	86	76	68	62	84	74	67	61	72	65	60	70	64	60	68	63	59	57		
5	80	68	60	54	78	67	59	53	65	58	53	63	57	52	61	56	52	50		
6	74	62	53	47	72	61	53	47	59	52	47	57	51	46	56	50	46	44		
7	69	56	48	42	67	55	48	42	54	47	42	52	46	41	51	45	41	39		
8	64	51	43	38	63	51	43	38	49	42	37	48	42	37	47	41	37	35		
9	60	47	39	34	59	47	39	34	46	39	34	45	38	34	44	38	34	32		
10	56	44	36	31	55	43	36	31	42	36	31	41	35	31	40	35	31	29		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204500

CATALOG NUMBER: LD6B40D010 EU6B30508040 6LBSB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	164.9	4.2
10°-20°	468.0	11.8
20°-30°	696.1	17.6
30°-40°	810.1	20.4
40°-50°	789.6	19.9
50°-60°	607.3	15.3
60°-70°	335.7	8.5
70°-80°	88.9	2.2
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1329.1	33.6
0°-40°	2139.1	54.0
0°-60°	3536.0	89.3
0°-90°	3961.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3961.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1748	
5°	1737	165
15°	1657	468
25°	1512	696
35°	1301	810
45°	1024	790
55°	678	607
65°	336	336
75°	75	89
85°	0	1
90°	0	



TEST NUMBER: P204500

CATALOG NUMBER: LD6B40D010 EU6B30508040 6LBSB1

CANDELA DISTRIBUTION (FULL):

0°	
0°	1747.5
2.5°	1747.5
5°	1737.4
7.5°	1722.4
10°	1712.3
12.5°	1682.2
15°	1657.1
17.5°	1632.0
20°	1596.8
22.5°	1561.7
25°	1511.5
27.5°	1461.3
30°	1411.0
32.5°	1355.8
35°	1300.6
37.5°	1230.3
40°	1170.0
42.5°	1104.7
45°	1024.4
47.5°	949.1
50°	863.7
52.5°	773.3
55°	677.9
57.5°	587.5
60°	502.2
62.5°	416.8
65°	336.4
67.5°	261.1
70°	190.8
72.5°	130.6
75°	75.3
77.5°	35.2
80°	5.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)