

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204397

Luminaire Tested: **LD6B40D010 EU6B30508040 6LBSGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204397
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B40D010 EU6B30508040 6LBSGPH1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH GRAPHITE HAZE TRIM
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57
W DL3-44.71 W DLE-39.33 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4134.8 lumens
Efficiency: N/A
Efficacy: 98.9 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.26
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204397

CATALOG NUMBER: LD6B40D010 EU6B30508040 6LBSGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P204397

CATALOG NUMBER: LD6B40D010 EU6B30508040 6LBSGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	111	107	103	100	108	105	102	99	101	98	96		97	95	93		93
2	102	95	89	84	100	93	88	83	90	85	82		87	83	80		84
3	94	85	78	72	92	83	77	71	80	75	70		78	73	69		75
4	87	76	68	62	85	75	67	62	72	66	61		70	65	60		68
5	80	68	60	54	78	67	60	54	65	59	53		63	58	53		62
6	74	62	54	48	73	61	53	48	59	52	47		58	52	47		56
7	69	57	48	43	68	56	48	43	54	47	42		53	47	42		52
8	65	52	44	38	63	51	44	38	50	43	38		49	42	38		48
9	60	48	40	35	59	47	40	35	46	39	35		45	39	34		44
10	57	44	37	32	56	44	36	32	43	36	31		42	36	31		41

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204397

CATALOG NUMBER: LD6B40D010 EU6B30508040 6LBSGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	180.8	4.4
10°-20°	507.5	12.3
20°-30°	740.3	17.9
30°-40°	844.2	20.4
40°-50°	809.8	19.6
50°-60°	620.2	15.0
60°-70°	340.3	8.2
70°-80°	90.5	2.2
80°-90°	1.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1428.6	34.6
0°-40°	2272.8	55.0
0°-60°	3702.7	89.5
0°-90°	4134.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4134.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1920	
5°	1906	181
15°	1801	508
25°	1608	740
35°	1350	844
45°	1052	810
55°	695	620
65°	342	340
75°	79	90
85°	0	1
90°	0	



TEST NUMBER: P204397

CATALOG NUMBER: LD6B40D010 EU6B30508040 6LBSGPH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	1920.4
2.5°	1915.5
5°	1905.5
7.5°	1890.7
10°	1870.8
12.5°	1836.1
15°	1801.3
17.5°	1761.6
20°	1717.0
22.5°	1662.4
25°	1607.8
27.5°	1553.2
30°	1483.7
32.5°	1419.2
35°	1349.8
37.5°	1280.3
40°	1210.8
42.5°	1136.4
45°	1052.0
47.5°	967.7
50°	878.3
52.5°	784.1
55°	694.7
57.5°	605.4
60°	511.1
62.5°	421.8
65°	342.4
67.5°	263.0
70°	193.5
72.5°	129.0
75°	79.4
77.5°	34.7
80°	9.9
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)