

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204294

Luminaire Tested: **LD6B40D010 EU6B30508040 6LBSWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204294
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B40D010 EU6B30508040 6LBSWH1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57
W DL3-44.71 W DLE-39.33 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4531.5 lumens
Efficiency: N/A
Efficacy: 108.4 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204294

CATALOG NUMBER: LD6B40D010 EU6B30508040 6LBSWH1

Luminous Intensity Polar Plot





TEST NUMBER: P204294

CATALOG NUMBER: LD6B40D010 EU6B30508040 6LBSWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			50
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			102
1	111	107	104	101	108	105	102	99		101	98	96			97	95	93			94
2	103	96	90	85	100	94	89	84		91	86	83			87	84	81			85
3	95	86	79	73	93	84	78	73		82	76	72			79	74	70			76
4	88	77	70	64	86	76	69	63		74	68	63			72	66	62			69
5	81	70	62	56	79	69	62	56		67	60	55			65	59	55			63
6	76	64	56	50	74	63	55	50		61	54	49			60	54	49			58
7	71	58	51	45	69	58	50	45		56	49	45			55	49	44			54
8	66	54	46	41	65	53	46	41		52	45	40			51	45	40			50
9	62	50	42	37	61	49	42	37		48	41	37			47	41	37			46
10	58	46	39	34	57	46	39	34		45	38	34			44	38	34			43

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204294

CATALOG NUMBER: LD6B40D010 EU6B30508040 6LBSWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	249.3	5.5
10°-20°	645.2	14.2
20°-30°	843.9	18.6
30°-40°	893.6	19.7
40°-50°	833.4	18.4
50°-60°	631.2	13.9
60°-70°	341.9	7.5
70°-80°	91.7	2.0
80°-90°	1.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1738.3	38.4
0°-40°	2631.9	58.1
0°-60°	4096.5	90.4
0°-90°	4531.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4531.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2703	
5°	2663	249
15°	2306	645
25°	1835	844
35°	1428	894
45°	1086	833
55°	709	631
65°	342	342
75°	79	92
85°	0	1
90°	0	



TEST NUMBER: P204294

CATALOG NUMBER: LD6B40D010 EU6B30508040 6LBSWH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	2702.6
2.5°	2692.6
5°	2662.9
7.5°	2598.4
10°	2514.1
12.5°	2414.9
15°	2305.8
17.5°	2181.9
20°	2072.8
22.5°	1948.8
25°	1834.8
27.5°	1720.7
30°	1611.6
32.5°	1517.4
35°	1428.1
37.5°	1338.9
40°	1254.6
42.5°	1170.3
45°	1086.0
47.5°	991.8
50°	897.5
52.5°	803.3
55°	709.1
57.5°	609.9
60°	515.7
62.5°	426.5
65°	342.2
67.5°	262.8
70°	193.4
72.5°	133.9
75°	79.3
77.5°	34.7
80°	9.9
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)