

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205218

Luminaire Tested: **LD6B40D010 EU6B30508040 6LBWLI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205218
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B40D010 EU6B30508040 6LBWLI1
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH SPECULAR CLEAR TRIM
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57
W DL3-44.71 W DLE-39.33 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4372.9 lumens
Efficiency: N/A
Efficacy: 104.6 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.18
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205218

CATALOG NUMBER: LD6B40D010 EU6B30508040 6LBWLI1

Luminous Intensity Polar Plot





TEST NUMBER: P205218

CATALOG NUMBER: LD6B40D010 EU6B30508040 6LBWLI1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	104	110	107	105	103	103	101	99		100	98	97		96
2	106	101	96	92	104	99	95	91	95	92	89		92	90	87		90
3	100	92	87	82	97	91	86	81	88	84	80		86	82	79		83
4	93	85	78	73	92	84	78	73	81	76	72		79	75	71		77
5	88	78	71	66	86	77	71	66	75	70	65		73	69	65		72
6	82	72	65	60	81	71	65	60	70	64	59		68	63	59		67
7	77	67	60	55	76	66	59	55	65	59	54		63	58	54		62
8	73	62	55	50	71	61	55	50	60	54	50		59	54	50		58
9	69	57	51	46	67	57	50	46	56	50	46		55	50	46		54
10	65	54	47	43	64	53	47	42	52	46	42		51	46	42		51

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205218

CATALOG NUMBER: LD6B40D010 EU6B30508040 6LBWLI1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	263.5	6.0
10°-20°	792.1	18.1
20°-30°	1194.1	27.3
30°-40°	1222.2	27.9
40°-50°	712.0	16.3
50°-60°	163.6	3.7
60°-70°	20.1	0.5
70°-80°	5.3	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2249.8	51.4
0°-40°	3471.9	79.4
0°-60°	4347.5	99.4
0°-90°	4372.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4372.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2732	
5°	2747	264
15°	2806	792
25°	2618	1194
35°	1983	1222
45°	917	712
55°	159	164
65°	15	20
75°	5	5
85°	0	0
90°	0	



TEST NUMBER: P205218

CATALOG NUMBER: LD6B40D010 EU6B30508040 6LBWLI1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2731.8
2.5°	2726.8
5°	2746.7
7.5°	2766.5
10°	2791.3
12.5°	2796.3
15°	2806.2
17.5°	2796.3
20°	2771.5
22.5°	2692.1
25°	2617.8
27.5°	2498.8
30°	2345.1
32.5°	2186.4
35°	1983.2
37.5°	1755.1
40°	1502.2
42.5°	1219.6
45°	917.2
47.5°	639.6
50°	421.4
52.5°	267.7
55°	158.7
57.5°	84.3
60°	44.6
62.5°	24.8
65°	14.9
67.5°	14.9
70°	9.9
72.5°	5.0
75°	5.0
77.5°	5.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)