

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204920

Luminaire Tested: **LD6B40D010 EU6B30509040 6LBCSMB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204920
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B40D010 EU6B30509040 6LBCSMB1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH CAST MATTE BLACK TRIM
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57
W DL3-44.71 W DLE-39.33 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3364.2 lumens
Efficiency: N/A
Efficacy: 80.5 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204920

CATALOG NUMBER: LD6B40D010 EU6B30509040 6LBCSMB1

Luminous Intensity Polar Plot






TEST NUMBER: P204920

CATALOG NUMBER: LD6B40D010 EU6B30509040 6LBCSMB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	111	107	103	100	108	104	101	98		100	98	95		96	94	92		93	91	90
2	102	95	89	84	99	93	87	83		89	85	81		86	82	79		83	80	77
3	93	84	77	71	91	83	76	70		80	74	69		77	72	68		74	70	67
4	86	75	67	61	84	74	66	61		71	65	60		69	63	59		67	62	58
5	79	67	59	53	77	66	59	53		64	57	52		62	56	52		61	55	51
6	74	61	53	47	72	60	52	46		58	51	46		57	50	46		55	50	45
7	68	55	47	41	67	55	47	41		53	46	41		52	45	41		50	45	40
8	64	51	43	37	62	50	42	37		49	42	37		48	41	37		46	41	36
9	60	47	39	33	58	46	39	33		45	38	33		44	38	33		43	37	33
10	56	43	35	30	55	43	35	30		42	35	30		41	34	30		40	34	30

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204920

CATALOG NUMBER: LD6B40D010 EU6B30509040 6LBCSMB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	134.4	4.0
10°-20°	382.8	11.4
20°-30°	575.4	17.1
30°-40°	682.8	20.3
40°-50°	675.7	20.1
50°-60°	530.7	15.8
60°-70°	297.5	8.8
70°-80°	83.6	2.5
80°-90°	1.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1092.6	32.5
0°-40°	1775.4	52.8
0°-60°	2981.8	88.6
0°-90°	3364.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3364.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1421	
5°	1418	134
15°	1358	383
25°	1249	575
35°	1095	683
45°	880	676
55°	598	531
65°	297	298
75°	72	84
85°	0	1
90°	0	



TEST NUMBER: P204920

CATALOG NUMBER: LD6B40D010 EU6B30509040 6LBCSMB1

CANDELA DISTRIBUTION (FULL):

0°	
0°	1420.6
2.5°	1415.7
5°	1418.1
7.5°	1406.1
10°	1391.6
12.5°	1374.7
15°	1357.8
17.5°	1336.1
20°	1307.2
22.5°	1278.3
25°	1249.3
27.5°	1218.0
30°	1177.0
32.5°	1136.0
35°	1095.0
37.5°	1046.7
40°	991.2
42.5°	938.2
45°	880.3
47.5°	815.2
50°	747.7
52.5°	670.5
55°	598.1
57.5°	516.1
60°	438.9
62.5°	369.0
65°	296.7
67.5°	233.9
70°	173.6
72.5°	118.2
75°	72.4
77.5°	36.2
80°	9.6
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)