

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205428

Luminaire Tested: **LD6B40D010 EU6B30509040 6LBSLI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205428
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B40D010 EU6B30509040 6LBSLI1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH SPECULAR CLEAR TRIM
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57
W DL3-44.71 W DLE-39.33 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3908.2 lumens
Efficiency: N/A
Efficacy: 93.5 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1.04
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205428

CATALOG NUMBER: LD6B40D010 EU6B30509040 6LBSLI1

Luminous Intensity Polar Plot





TEST NUMBER: P205428

CATALOG NUMBER: LD6B40D010 EU6B30509040 6LBSLI1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			50
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			102
1	111	107	104	101	109	105	102	99		101	99	96			97	95	93			94
2	103	96	91	86	100	94	89	85		91	87	83			88	84	81			85
3	95	86	79	74	93	85	78	73		82	76	72			79	75	71			77
4	88	78	70	64	86	77	69	64		74	68	63			72	67	62			70
5	82	71	63	57	80	70	62	57		67	61	56			66	60	55			64
6	76	64	56	51	74	63	56	51		62	55	50			60	54	50			59
7	71	59	51	46	70	58	51	45		57	50	45			55	49	45			54
8	67	54	47	41	65	54	46	41		52	46	41			51	45	41			50
9	63	50	43	38	61	50	43	38		49	42	38			48	42	37			47
10	59	47	40	35	58	46	39	35		45	39	35			45	39	34			44

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205428

CATALOG NUMBER: LD6B40D010 EU6B30509040 6LBSLI1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	227.3	5.8
10°-20°	578.5	14.8
20°-30°	737.8	18.9
30°-40°	765.1	19.6
40°-50°	705.0	18.0
50°-60°	530.3	13.6
60°-70°	286.3	7.3
70°-80°	76.8	2.0
80°-90°	1.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1543.6	39.5
0°-40°	2308.7	59.1
0°-60°	3544.0	90.7
0°-90°	3908.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3908.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2466	
5°	2429	227
15°	2064	579
25°	1603	738
35°	1221	765
45°	918	705
55°	594	530
65°	286	286
75°	66	77
85°	0	1
90°	0	



TEST NUMBER: P205428

CATALOG NUMBER: LD6B40D010 EU6B30509040 6LBSLI1

CANDELA DISTRIBUTION (FULL):

0°	
0°	2466.2
2.5°	2457.9
5°	2428.9
7.5°	2374.9
10°	2279.4
12.5°	2183.9
15°	2063.5
17.5°	1951.4
20°	1835.1
22.5°	1714.7
25°	1602.6
27.5°	1494.7
30°	1395.0
32.5°	1303.7
35°	1220.7
37.5°	1141.8
40°	1067.0
42.5°	988.2
45°	917.6
47.5°	838.7
50°	759.8
52.5°	676.8
55°	593.7
57.5°	510.7
60°	431.8
62.5°	357.1
65°	286.5
67.5°	220.1
70°	161.9
72.5°	112.1
75°	66.4
77.5°	29.1
80°	8.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)