

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P202549

Luminaire Tested: **LD6B40D010 EU6B30509040 6LBSWMH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P202549
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B40D010 EU6B30509040 6LBSWMH1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH WARM HAZE TRIM
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57
W DL3-44.71 W DLE-39.33 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3809.6 lumens
Efficiency: N/A
Efficacy: 91.1 lumens/watt
Spacing Criteria (0/90/45): 0.97 / 0.97 / 1.1
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P202549

CATALOG NUMBER: LD6B40D010 EU6B30509040 6LBSWMH1

Luminous Intensity Polar Plot




TEST NUMBER: P202549
CATALOG NUMBER: LD6B40D010 EU6B30509040 6LBSWMH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	88		
2	103	96	90	85	100	94	89	84	91	86	82	87	84	81	84	81	79	77		
3	95	86	79	73	92	84	78	73	81	76	71	79	74	70	76	72	69	67		
4	88	77	70	64	86	76	69	63	74	67	62	71	66	62	69	65	61	59		
5	81	70	62	56	79	69	61	56	67	60	55	65	59	55	63	58	54	52		
6	76	64	56	50	74	63	55	50	61	54	49	59	53	49	58	53	48	47		
7	70	58	50	45	69	57	50	45	56	49	44	55	48	44	53	48	44	42		
8	66	54	46	40	64	53	45	40	52	45	40	50	44	40	49	44	40	38		
9	62	49	42	37	61	49	42	37	48	41	37	47	41	36	46	40	36	35		
10	58	46	39	34	57	45	38	34	45	38	34	44	38	33	43	37	33	32		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P202549

CATALOG NUMBER: LD6B40D010 EU6B30509040 6LBSWMH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	203.8	5.4
10°-20°	532.8	14.0
20°-30°	706.5	18.5
30°-40°	753.5	19.8
40°-50°	704.4	18.5
50°-60°	537.1	14.1
60°-70°	292.2	7.7
70°-80°	78.4	2.1
80°-90°	0.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1443.1	37.9
0°-40°	2196.6	57.7
0°-60°	3438.1	90.2
0°-90°	3809.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3809.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2203	
5°	2173	204
15°	1900	533
25°	1538	706
35°	1204	754
45°	917	704
55°	604	537
65°	292	292
75°	68	78
85°	0	1
90°	0	



TEST NUMBER: P202549

CATALOG NUMBER: LD6B40D010 EU6B30509040 6LBSWMH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	2203.0
2.5°	2196.0
5°	2172.6
7.5°	2123.6
10°	2067.6
12.5°	1988.3
15°	1899.6
17.5°	1810.9
20°	1715.2
22.5°	1624.2
25°	1537.9
27.5°	1446.9
30°	1360.5
32.5°	1276.5
35°	1204.2
37.5°	1131.8
40°	1057.1
42.5°	989.5
45°	917.1
47.5°	837.8
50°	763.1
52.5°	683.8
55°	604.4
57.5°	518.1
60°	438.7
62.5°	364.0
65°	291.7
67.5°	226.4
70°	165.7
72.5°	114.3
75°	67.7
77.5°	30.3
80°	7.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)